

## Ty-Gun ERG 50 / Ty-Gun ERG 120 Cable tie pliers

TY-GUN ERG 50 / TY-GUN ERG 120 cable tie pliers allows quick and economical assembly of cable ties.

### Info

Improved push ring and optimized blade and drawbar suspension



Assembly time



Robust

### Benefits

- Tip can be rotated 360° for easy assembly
- Adjustable tension-setting and automatic cutting mechanism
- Large feed-opening (25,4 mm width) facilitates inserting of the cable ties
- Ergonomic design (rounded design) and user-friendliness
- Reduced user stress and strain

### Application range

- Cable tie gun for plastic cable ties
- Allows quick and economical binding, fixing and mounting of plastic cable ties
- Increased service life due to the optimal tension setting for each cable tie
- Waste prevention on the floor- cable tie rests were prevented from falling down

### Product features

- Adjustable grip diameter enables adaption to the hand size of the user
- Anti-recoil mechanism prevents shaking
- Easy and practical storage of the replacement blades inside the tool (one replacement blade is included inside the tool)
- Lightweight
- Nose made of stainless steel guarantees a longer lifetime of the tool

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000453

ETIM 5.0 Class-Description: Cable tie tool

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000453

ETIM 6.0 Class-Description: Cable tie tool

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**Ty-Gun ERG 50 / Ty-Gun ERG 120 Cable tie pliers**

Caution:	Tension is manually adjustable
Note:	Length x width x height: 178x127x38 mm ERG 50: 65-83 N for setting 1, 175-220 N for setting 8 ERG 120: 175-250 N for setting 1, 450-580 N for setting 8
Colour delivered:	ERG 50: Black head ERG 120: Orange head
Material:	Shock-resistant polymer Soft rubber grip

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**Ty-Gun ERG 50 / Ty-Gun ERG 120 Cable tie pliers**

Article number	Article description	For cable ties	Cable tie width (mm)	Weight (kg)	Pieces / PU
Ty-Gun ERG 50					
62120120	Ty-Gun ERG 50	Plastic	2.4 - 4.8	0.26	1
Ty-Gun ERG 120					
62120125	Ty-Gun ERG 120	Plastic	4.8 - 7.6	0.278	1
62120126	Ty-Gun ERG 120B spare blades	Plastic	4.8 - 7.6	-	1