

STAR STRIP stripping tool

Stripping tool for cable diameters up to 40 mm, interchangeable hooks, reliable and durable, also for problematic insulation as PTFE, TPE, Fluorpolymere and PUR

Info

Special polished stripping knife is suitable for problematical insulation materials such as PUR, fluoropolymers, glass fibre, TPE and rubber



Benefits

- Large application range thanks to the interchangeable hooks
- Suitable for circular, longitudinal and spiral cuts
- High quality of the blade ensures a good stripping result also for tough insulation materials
- Robust body, long durability- tested for more than 100.000 stripping operations
- High ergonomics and user-friendliness (inter alias due to a lightweight construction)

Application range

Adjustable stripping tool for round cables made with various insulation materials (as PVC, PTFE, rubber or PUR)
Through the interchangeable hooks, the tool can be used for cables with a diameter of 4.5 - 25 mm and 20 - 40 mm

Product features

- The depth of the blade is adjustable by rotating the upper part of the tool
- Specific locking positions for circular, longitudinal or spiral cuts
- The blade automatically returns to its start position at the end of a stripping process, thus reducing the possibility of breaking the blade.
- No special tool is required to replace the hook (other hook is used for releasing the assembled hook)

Note

Spare blades are available and can be stored in a compartment of the tool

Included

61735820: Tool with blade, small and large hook without spare blade

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000163

ETIM 5.0 Class-Description: Cable stripping tool

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000163

ETIM 6.0 Class-Description: Cable stripping tool

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

STAR STRIP stripping tool

| | |
|-------------------|---|
| Weight: | STAR STRIP with large hook: 116 g |
| Length: | Dimensions LxHxB: Small hook: 150x42x30.5 mm Big hook: 167x52x30.5 mm |
| Colour delivered: | Black |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

STAR STRIP stripping tool

| Article number | Article designation | For outer diameter (mm) | Length (mm) | Pieces / PU |
|---|------------------------------|-------------------------|-------------|-------------|
| STAR STRIP with one blade, small and big hook (but without replacement blade) | | | | |
| 61735820 | STAR STRIP | 4.5 - 40 | 150 | 1 |
| Spare parts | | | | |
| 61735821 | STAR STRIP spare blade | - | - | 1 |
| 61735822 | STAR STRIP spare hook, small | 4.5 - 25 | - | 1 |
| 61735823 | STAR STRIP spare hook, large | 20 - 40 | - | 1 |

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16