

SKINDICHT® MA-M/PG

SKINDICHT® MA-M/PG, adapter, enables the use of PG accessories in metric threads



Mechanical resistance



Robust

Benefits

Allows the easy transition from a metric male thread to a PG female thread.

Withstands temperatures up to +200 °C.

Available for thread sizes up to PG42 or up to M63.

Mold A in easy-grip knurled design for easy screwing in of the adapter even in oily environments; mold B in smooth design.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

Application range

For applications with different types of threads.

Withstands high chemical and mechanical stress.

Suitable for outdoor use.

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

On request:

with O-ring fitted

Material:

Nickel-plated brass

Temperature range:

-60 °C to +200 °C

Last Update (16.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® MA-M/PG

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® MA-M/PG

Article number	Thread, male M1	Thread, female PG	Pieces / PU
SKINDICHT® MA-M / PG			
52104200	16 x 1.5	7	100
52104200LF	16 x 1.5	7	100
52104210	20 x 1.5	9	50
52104210LF	20 x 1.5	9	50
52104220	25 x 1.5	11	50
52104230	25 x 1.5	13.5	50
52104240	25 x 1.5	16	50
52104250	32 x 1.5	16	25
52104260	32 x 1.5	21	25
52104270	40 x 1.5	21	25
52104280	50 x 1.5	29	10
52104290	63 x 1.5	36	10
52104300	63 x 1.5	42	10
52104220LF	25 x 1.5	11	50
52104230LF	25 x 1.5	13.5	50
52104240LF	25 x 1.5	16	50
52104250LF	32 x 1.5	-	25
52104260LF	32 x 1.5	21	25
52104270LF	40 x 1.5	21	25
52104280LF	50 x 1.5	29	10
52104290LF	63 x 1.5	36	10
52104300LF	63 x 1.5	42	10