


SKINTOP® COLD

SKINTOP® COLD, metric brass cable gland, high cold-resistance and cold impact resistance, high mechanical stability

Info

For extreme sub-zero temperatures



-  Good chemical resistance
-  Cold-resistant
-  Corrosion-resistant
-  Mechanical resistance
-  Temperature-resistant

Benefits

High cold-resistance
Cold impact resistance
High mechanical stability
Optimum strain relief
Wide, variable clamping ranges

Application range

In areas where mechanical stability and high cold-resistance are critical
Air-conditioning technology
Freezing plants, cold storage
Offshore sector
Plant engineering

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® COLD

Norm references / Approvals

UL File Nr. E79903

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Caution:

Refer to Appendix T21 for the installation dimensions and torques

Material:

Body: nickel-plated brass

Insert: special polyamide

Sealing ring: silicone

O-ring: silicone

Protection rating:

IP 68 - 10 bar (M12 - M20)

IP 68 - 5 bar (M25 - M63)

NEMA Type 1, 2, 4x, 6, 12

Temperature range:

-70°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® COLD

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
SKINTOP® COLD						
53113500	M 12 x 1,5	3.5 - 7	16	26.5	6.5	100
53113510	M 16 x 1,5	4.5 - 10	20	33.0	7	100
53113520	M 20 x 1,5	7 - 13	24	37.0	8	50
53113530	M 25 x 1,5	9 - 17	29	38.5	8	25
53113540	M 32 x 1,5	11 - 21	36	45.5	9	25
53113550	M 40 x 1,5	19 - 28	45	48.0	9	10
53113560	M 50 x 1,5	27 - 35	54	55.5	10	5
53113570	M 63 x 1,5	34 - 45	67	67.0	15	5