

## SKINDICHT® JT PTFE metric

SKINDICHT® JT PTFE metric, sealing rings, suitable for foodstuffs, resistant to oil, water, alkaline solutions, acids, solvents etc



Food & Beverage



Good chemical resistance



Acid-resistant



Temperature-resistant

### Benefits

Resistant to oil, water, alkaline solutions, acids, solvents, etc.  
Suitable for foodstuffs

### Application range

PTFE sealing disks for SKINTOP® and SKINDICHT® cable glands

### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001181

ETIM 5.0 Class-Description: Sealing ring

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001181

ETIM 6.0 Class-Description: Sealing ring

Colour delivered:

White

Material:

PTFE

Temperature range:

-120 °C to +250 °C

Short-term: up to +300 °C

## SKINDICHT® JT PTFE metric

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® JT PTFE metric**

| Article number            | Article designation / size | Inner Ø (mm) | Thickness (mm) | Outer Ø (mm) | Pieces / PU |
|---------------------------|----------------------------|--------------|----------------|--------------|-------------|
| SKINDICHT® JT PTFE metric |                            |              |                |              |             |
| 53801030                  | M 12                       | 12.1         | 2.0            | 16.6         | 100         |
| 53801040                  | M 16                       | 16.1         | 2.0            | 21.1         | 100         |
| 53801050                  | M 20                       | 20.1         | 2.0            | 27.5         | 100         |
| 53801060                  | M 25                       | 25.1         | 3.0            | 33.4         | 50          |
| 53801070                  | M 32                       | 32.1         | 3.0            | 40.3         | 50          |
| 53801080                  | M 40                       | 40.2         | 3.0            | 51.5         | 25          |
| 53801090                  | M 50                       | 50.2         | 3.0            | 61.6         | 25          |
| 53801100                  | M 63                       | 63.2         | 3.0            | 73.9         | 25          |