

SKINDICHT® JT PTFE PG

SKINDICHT® JT PTFE PG, sealing ring, suitable for foodstuffs, PG thread, resistant to oil, water, alkaline solutions, acids, solvents



Food & Beverage



Good chemical resistance



Acid-resistant



Temperature-resistant

Benefits

Resistant to oil, water, alkaline solutions, acids, solvents, etc.
Suitable for foodstuffs

Application range

PTFE sealing disks for SKINTOP® and SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001181

ETIM 5.0 Class-Description: Sealing ring

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001181

ETIM 6.0 Class-Description: Sealing ring

Colour delivered:

White

Material:

PTFE

Temperature range:

-120°C to +250°C

Short-term: up to +300°C

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® JT PTFE PG

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® JT PTFE PG

Article number	Article designation / size	Internal Ø/external Ø (mm)	Thickness (mm)	Outer Ø (mm)	Pieces / PU
SKINDICHT® JT PTFE					
53801035	PG 7	12.5 / 16.5	2.0	16.5	100
53801045	PG 9	15.2 / 19.0	2.0	19.0	100
53801055	PG 11	18.6 / 22.5	2.0	22.5	100
53801065	PG 13,5	20.4 / 25.0	2.0	25.0	100
53801075	PG 16	22.5 / 27.0	2.0	27.0	100
53801085	PG 21	28.3 / 33.5	3.0	33.5	50
53801095	PG 29	37.0 / 43.5	3.0	43.5	50
53801105	PG 36	47.0 / 55.0	3.0	55.0	25
53801115	PG 42	54.0 / 63.0	3.0	63.0	25
53801125	PG 48	59.3 / 69.0	3.0	69.0	25