

ETHERLINE® EC Flex Cat.5e M8

Industrial Ethernet EC Patchcord M8

Industrial Ethernet Patchcord, EtherCat, Cat.5e, plug M8, PVC, flexible


Info

For EtherCAT applications

Other types are available at

www.lappgroup.com/assemblyfinder

or on request



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Assembly time



Interference signals



Waterproof

Benefits

Non-permanent connections allow for easy change of equipment

For directly connecting two electric components

Flexible use

Application range

Suitable for use in industrial applications

especially for EtherCat applications

For indoor use

Automation technology

Last Update (01.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® EC Flex Cat.5e M8

Product features

Meets the requirements according to Cat. 5e and class D
2pair: 10/100 Mbit/s for Industrial Ethernet

Product Make-up

Stranded conductor, 7-wire, 2x2xAWG26/7
Overall screening with copper braid and plastic-laminated aluminium foil
Pre-assembled patchcords with M8 connectors
Colour: green (based on RAL 6018)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002599 ETIM 5.0 Class-Description: Patch cord copper (twisted pair) industry
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002599 ETIM 6.0 Class-Description: Patch cord copper (twisted pair) industry
Minimum bending radius:	Fixed installation: 4 x outer diameter Moved: 10 x outer diameter
Protection rating:	IP 67
Characteristic impedance:	100 $\Omega \pm 15\%$
Temperature range:	Fixed installation: -30°C to +80°C Flexing: -5°C to +50°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Other lengths and types of connectors are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ETHERLINE® EC Flex Cat.5e M8

Article number	Length (m)
straight plug M8 on straight plug M8	
2171300	0.5
2171301	1
2171302	2
2171303	3
2171304	5
2171305	7
2171306	10
2171307	15
2171308	20
angled plug M8 on straight plug M8	
2171350	0.5
2171351	1
2171352	2
2171353	3
2171354	5
2171355	7
2171356	10
2171357	15
2171358	20
straight plug M8 on free conductor end	
2171320	0.5
2171321	1
2171322	2
2171323	3
2171324	5
2171325	7
2171326	10
2171327	15
2171328	20
angled plug M8 on free conductor end	
2171370	0.5
2171371	1
2171372	2
2171373	3

Last Update (01.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

ETHERLINE® EC Flex Cat.5e M8

Article number	Length (m)
2171374	5
2171375	7
2171376	10
2171377	15
2171378	20

ETHERLINE® EC Flex Cat.5e M8

