

UNITRONIC® BUS IS

ISOBUS cables for use in agricultural vehicles

Data transmission at agricultural vehicles. Resistant against oil, benzine, diesel and UV. Acc. To ISO 11783-2:2012. Temperature range from -40°C bis +85°C

Info

Lapp cable is member of the AEF - Agricultural Industry Electronics Foundation



Suitable for outdoor use



Halogen-free



Cold-resistant



Mechanical resistance



Oil-resistant



UV-resistant

Benefits

Cable according ISOBUS standard (ISO 11783-2) for use in agricultural vehicles.

HYBRID: cable for data transmission + power supply

Application range

For outdoor applications

Connection cable between tractor and pulled machinery

Product features

Flame-retardant according to IEC standard 60332-1

UV-resistant

Resistant against oil, benzine and diesel

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® BUS IS

PUR (Polyurethane) Version with increased robustness

Norm references / Approvals

ISO 11783-2:2012

Product Make-up

Fine-wired copper conductor of bare copper strands in line with conductor class 5 acc. IEC 60228

4x 0,5 mm² (red, yellow, black, green)

2x 2,5 mm² (red, black)

2x 6 mm² (red, black)

Outer sheath: PUR and PVC, black (RAL 9005)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Peak operating voltage:	60 V
Minimum bending radius:	Fixed installation: 10 x outer diameter Flexing: 15 x outer diameter
Test voltage:	0,5 mm - 2,5 mm ² core / core = 1,5 kV; 6 - 10 mm ² core / core = 2,5 kV
Characteristic impedance:	Characteristic impedance: 75 ohm
Temperature range:	PUR: -40°C to +85°C PVC: -30°C to +85°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UNITRONIC® BUS IS

Article number	Article designation	Number of cores/pairs and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)
PUR				
2170561	UNITRONIC® BUS IS PUR 2x6+2x2,5+1x4x0,5	2x6+2x2,5+1x4x0,5	15.6	182.4
PVC				
2170560	UNITRONIC® BUS IS PVC	2x6+2x2,5+1x4x0,5	15.6	182.4