

## JE-LiYCY...BD

Screened data transmission cable for industrial electronics

JE-LiYCY...BD - installation cable for industrial electronics, VDE 0815, 7-wire conductor, bundle laying, screened, PVC

### Info

In accordance with DIN VDE 0815



Interference signals

### Benefits

Overall braid minimises electrical interference

Decoupling of circuits by means of twisted-pair (TP) design (crosstalk effects)

### Application range

Connection cable for use in electronics and in measurement, control and signal applications

This cable is also used as a pulse and data transmission cable

JE-LiYCY...BD has also proved to be an efficient connection cable for telephone systems, e.g. paging and intercom systems.

For fixed installation on and under plaster, in dry and damp rooms

### Product features

The 2-pair version (2 x 2 x 0.5) is twisted into a star quad

Flame-retardant according IEC 60332-1-2

JE-LiYCY...BD EB:

For intrinsically safe circuits (type of protection i - intrinsic safety) according to IEC 60079-14:2013 / EN 60079-14:2014 / VDE 0165-1:2014, section 16.2.2

### Norm references / Approvals

In accordance with DIN VDE 0815

type JE-LiYCY...BD

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## JE-LiYCY...BD

### Product Make-up

7-wire bare stranded copper conductor

Core insulation made of PVC

2 cores twisted into a pair, and 4 pairs into units/ bundles (for 2 x 2 x 0.5 as star quad cable)

Bundles twisted in layers,

foil wrapping,

screening braid made of tinned copper wires

Outer sheath made of PVC

Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000829 ETIM 5.0 Class-Description: Signal-/telecommunications cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000829 ETIM 6.0 Class-Description: Signal-/telecommunications cable
Core identification code:	according to VDE 0815, refer to Appendix T10
Mutual capacitance:	max. 100 nF/km
Coupling:	approx. 200 pF/100 m
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Multi-wire, 7 x 0.3mm
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 5 x outer diameter
Test voltage:	Core/core: 500 V Core/screen: 2000 V
Loop resistance:	max. 78.4 ohm/km
Temperature range:	Occasional flexing: -5 °C to +50 °C Fixed installation: -30 °C to +70 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

\* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**JE-LiYCY...BD**

Article number	Number of pairs and conductor cross section (mm <sup>2</sup> )	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
JE-LiYCY...BD				
0034200	2 x 2 x 0.5	6.6	51	70
0034201	4 x 2 x 0.5	8.5	87	155
0034202	8 x 2 x 0.5	11.7	144	260
0034208	12 x 2 x 0.5	12.8	195	340
0034203	16 x 2 x 0.5	13.9	249	430
0034210	20 x 2 x 0.5	15.1	298	495
0034204	24 x 2 x 0.5	16.4	348	605
0034212	32 x 2 x 0.5	21	441	738