

## EPIC® MC 2.5 machined contacts

For inserts and modules of the EPIC® rectangular connectors

The machined contacts for conductor cross-section from 0.5 to 4 mm<sup>2</sup> are available as female and male pins.

### Info

silver plated and passivated contacts



### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC 2.5 machined contacts

| Article number | Article description | Version | Conductor cross-section (mm²) | Cross-section identification | Surface | Stripping length (mm) | Pieces / PU |
|----------------|---------------------|---------|-------------------------------|------------------------------|---------|-----------------------|-------------|
| Contacts       |                     |         |                               |                              |         |                       |             |
| 1121300C       | MC 2.5 machined     | male    | 0.5                           | -                            | Ag      | 7.8                   | 100         |
| 1121800C       | MC 2.5 machined     | female  | 0.5                           | -                            | Ag      | 7.8                   | 100         |
| 1121310C       | MC 2.5 machined     | male    | 1                             | 1                            | Ag      | 7.8                   | 100         |
| 1121810C       | MC 2.5 machined     | female  | 1                             | 1                            | Ag      | 7.8                   | 100         |
| 1121320C       | MC 2.5 machined     | male    | 1.5                           | 2                            | Ag      | 7.8                   | 100         |
| 1121820C       | MC 2.5 machined     | female  | 1.5                           | 2                            | Ag      | 7.8                   | 100         |
| 1121330C       | MC 2.5 machined     | male    | 2.5                           | 3                            | Ag      | 7.8                   | 100         |
| 1121830C       | MC 2.5 machined     | female  | 2.5                           | 3                            | Ag      | 7.8                   | 100         |
| 1121340C       | MC 2.5 machined     | male    | 4                             | -                            | Ag      | 7.8                   | 100         |
| 1121840C       | MC 2.5 machined     | female  | 4                             | -                            | Ag      | 7.8                   | 100         |