


EPIC® H-B 10 TGH-RO

Housing design H-B. The industry standard.

The housing for rectangular connectors has a direct cable entry and pivots for a single lever. The housing is suitable for use in investment construction.

Info

Non-slip ridges for comfortable disconnecting
More interior space for wiring
Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The smallest housing with single and double lever. The right housing is available for every application

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 10 TGH-RO

Product features

Hood, high version
Reels for single lever
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 10 TGH-RO

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (straight cable entry, bolts for single lever, high version)					
70044200	H-B 10 TGH-RO 21	-	21	yes	10
70044400	H-B 10 TGH-RO 29	-	29	yes	10
79044200	H-B 10 TGH-RO M25	25	-	-	10
79044400	H-B 10 TGH-RO M32	32	-	-	10