

EPIC® MC Module: 10pole stamped

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

The 10-pole module with pressed contacts ensures the high flexibility connector, thanks to multiple functions. It can be used, for example, in investment construction.

Info

Suitable for processing with contacts on reel
for automated production with crimping machine



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

Benefits

The mix of different functions in one plug guarantees high flexibility
Assembly of individual connectors, suitable for different applications

Application range

Plant engineering
Printing machines
Control engineering

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial)

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MC Module: 10pole stamped

| | |
|--------------------------------|---|
| | connector) |
| Rated voltage (V): | 250 V |
| Rated current (A): | max. 10 A |
| Pollution degree: | 3 |
| Contact resistance: | < 2 mOhm |
| Contacts: | Copper alloy, hard silver/gold-plated |
| Number of contacts: | 10 |
| Termination methods: | Crimp termination: 0.14 - 2.5 mm ² |
| Cycle of mechanical operation: | 100 |
| VDE-tested: | UL-tested: UL File Number: E75770 |
| Temperature range: | -40°C to +100°C, short-term up to +125°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC Module: 10pole stamped

| Article number | Article description | Contact type | Number of operating contacts | Slots | Pieces / PU |
|----------------|---------------------|--------------|------------------------------|-------|-------------|
| Module: 10-pin | | | | | |
| 10383400 | MCS 10 CG | male | 10 | 1 | 10 |
| 10383500 | MCB 10 CG | female | 10 | 1 | 10 |

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16