

EPIC® MC Module: HE 4pole

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

The combination of a greater number of functions in this connector guarantees a high level of flexibility and it can therefore be used, for example, in printing presses.

Info

Lever for rapid removal of the module



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

Benefits

The mix of different functions in one plug guarantees high flexibility
Assembly of individual connectors, suitable for different applications

Application range

Plant engineering
Printing machines
Control engineering

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Rated voltage (V):

630 V

Rated current (A):

25 A

Last Update (30.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MC Module: HE 4pole

Pollution degree:	3
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	4
Termination methods:	Crimp termination: 0.5 - 4.0 mm ²
Cycle of mechanical operation:	100
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC Module: HE 4pole

Article number	Article description	Contact type	Number of operating contacts	Slots	Pieces / PU
Module: 4-pin HE					
10399000	MCS 4 CM	male	4	1	10
10399100	MCB 4 CM	female	4	1	10