


EPIC® H-B 16 TSB






Housing design H-B. The industry standard.

The universal metal housing with 2 double levers and a side cable entry is ideal for lighting and sound system applications.

Info

Non-slip ridges for comfortable disconnecting
For connection with counterpart with integrated cover
NEMA 250, UL50E: 12, 4 (latched)



-  Supplementary automation components from Lapp
-  Mechanical and plant engineering
-  Mechanical resistance
-  Robust
-  Waterproof

Benefits

The housing standard. Wide choice for all applications
Double lever version with 2 levers for increased safety

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 16 TSB

Product features

Hood, low version
Dual levers
Side cable entry
Versions with neck

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR |
| Protection rating: | IP 65 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770 |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 16 TSB

| Article number | Article description | M | PG | Neck | Pieces / PU |
|--|---------------------|----|----|------|-------------|
| H-B housing: hood (side cable entry, double lever) | | | | | |
| 10083000 | H-B 16 TSB 21 | - | 21 | yes | 5 |
| 19083000 | H-B 16 TSB M25 | 25 | - | yes | 5 |