

ÖLFLEX® PLUG H03VV-F Net Connection Cable*

PVC net connection cable for electrical devices

ÖLFLEX® PLUG H03VV-F Net connecting cable, PVC, 3G0,75, 1.end angled earthing-type plug with double earthed contact/2.end IEC coupling or dismantled

Info

Other colours and designs are available upon request



Application range

Electrical devices

Product features

For additional information regarding international plugs, please refer to our cable configurator at www.lappkabel.de

Apart from the cable related application restrictions to be paid attention to according to the application standard EN 50565-2 for this PVC cable H03VV-F, the fact that brighter outer sheath colours deviating from black significantly reduce the UV resistance of the outer sheath and, thus, the outdoor usability of the entire, finished cable has to be respected, too

Product Make-up

1st end: Gated, right-angled earthing-type plug with double earthing contact

Other end: 30 mm dismantled, with protection sleeves for the ends of the conductor

Alternatively, on request: 1st end with moulded right-angled earthing-type plug with twin earthed contact, 2nd end with moulded, straight IEC coupling (see image)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001576

ETIM 5.0 Class-Description: Power cord

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001576

ETIM 6.0 Class-Description: Power cord

Core identification code:

HD 308/VDE 0293-308: 3-core with protective conductor

Conductor stranding:

Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5

Nominal voltage:

U0: 250 V AC

Last Update (28.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® PLUG H03VV-F Net Connection Cable*

Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor
Temperature range:	5 °C to 60 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Please observe the safety information as per DIN VDE 0620-1, Plugs and socket-outlets for household and similar purposes - Part 1: General requirements, appendix E: "Installation only by persons with the relevant electrotechnical expertise and experience!"

ÖLFLEX® PLUG H03VV-F Net Connection Cable*

Article number	Number of cores and mm ² per conductor	Colour	Outer diameter [mm]	Length (m)	Copper index kg/1.000 pieces
1st end: moulded right-angled earthing-type plug with double earthed contact 2nd end: 30 mm stripped, with conductor end sleeves					
70261130	3 G 0.75	black	5.4 - 6.8	1.5	32.4
70261131	3 G 0.75	black	5.4 - 6.8	2	43.2
70261132	3 G 0.75	black	5.4 - 6.8	3	64.8
70261136	3 G 0.75	grey	5.4 - 6.8	1.5	32.4
70261137	3 G 0.75	grey	5.4 - 6.8	2	43.2
70261138	3 G 0.75	grey	5.4 - 6.8	3	64.8
70261133	3 G 0.75	white	5.4 - 6.8	1.5	32.4
70261134	3 G 0.75	white	5.4 - 6.8	2	43.2
70261135	3 G 0.75	white	5.4 - 6.8	3	64.8