

ÖLFLEX® SERVO 7TCE

Multi-listed, flexible servo cable with optional pairs for brake and temperature sensor


ÖLFLEX® SERVO 7TCE - screened servo cable for fixed installation or occasional flexing with UL TC-ER.

Info

Servo motor and drive connections

Wide application range (NFPA 70/NEC)/ compliance with NFPA 79 for industrial machinery

EMC-compliant



Flame-retardant



Mechanical resistance



Oil-resistant



Interference signals



UV-resistant

Benefits

One common cable for multiple circuits

Multi-standard certification reduces part varieties and saves costs

Cost-saving, easy installation due to omission of closed raceways (suitable for open wiring)

Low capacitance design enables longer cable connection between frequency converter and motor

UL TC-ER and c(UL) C1C/TC approved

Application range

Connecting cable between servo controller and motor

For fixed installation or applications with occasional movements

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® SERVO 7TCE

Class 1 Division 2 per NEC Articles 336, 501
Plant engineering
Industrial machinery and machine tools

Product features

Oil-resistant according to UL OIL RES I & II
Flame-retardant according to CSA FT4
UL Vertical-Tray Flame Test
-40°C Cold Bend; -25°C Cold Impact; 90°C Wet or Dry
Sunlight Resistant; Direct Burial

Norm references / Approvals

UL TC-ER (exposed run) per UL 1277
Class 1 Division 2 per NEC Articles 336, 501
Flexible Motor Supply Cable per UL 2277
c(UL) CIC FT4 (18AWG - 14AWG);
cRU AWM I/II A/B FT4

Product Make-up

Fine-wire, bare copper conductor
Core insulation: XLPE
Individual design depending on the item: power cores without or with one or two individually screened control core pairs twisted together in short lay lengths
Tinned-copper braiding
Outer sheath: Specially formulated thermoplastic elastomer (TPE), orange

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000057 ETIM 5.0 Class-Description: Low voltage power cable
Core identification code:	Power cores: black with marking U/L1/C/L+; V/L2; W/L3/D /L-; GN/YE protective conductor Optional designs with one pair of control cores: black; white Two pairs of control cores: black with white numbers: 5, 6, 7, 8
Certifications:	USA: UL TC-ER, Flexible Motor SupplyCanada: c(UL) CIC/TC FT4, cRU AWM I/II A/B FT4
Conductor stranding:	Fine wire
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	UL TC: 600V UL Flexible Motor Supply: 1000V c(UL) CIC/TC: 600V cRU AWM: 1000V IEC U0/U: 600/1000 V
Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor
Temperature range:	Occasional flexing: -25°C to +90°C Fixed installation: -40°C to +90°C

ÖLFLEX® SERVO 7TCE

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 610 m drum or 8 x 76 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® SERVO 7TCE

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
700730	4 G 1,5	9.8	87.81	143