

ÖLFLEX® SOLAR H1 BUR

H1Z2Z2-K/EN 50618 solar cable, Burial in ground, AD8, Dca


ÖLFLEX[®] SOLAR H1 BUR - TÜV-certified H1Z2Z2-K solar cable by LAPP per EN 50618/ IEC 62930, UL 854
Crushing- & Impact-Resistance, AD8, Burial in ground, CPR Dca

Info

AD8 - Permanent Submersion

Tested Burial in Ground

Dca classified per CPR



e-Mobility



Mechanical and plant engineering



Solar Energy



Wind Energy



Suitable for outdoor use



Good chemical resistance



Flame-retardant



Halogen-free

Last Update (16.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® SOLAR H1 BUR



Cold-resistant



Corrosion-resistant



Mechanical resistance



Assembly time



Low weight



Space requirement



Robust



Acid-resistant



Reliability



Voltage



Temperature-resistant



UV-resistant



Waterproof



Variety of approval certifications



Benefits

Halogen-free core insulation and sheath compound to meet special fire protection requirements

Transverse watertightness allows permanent submersion in shallow, uncontaminated water: AD8 in accordance with IEC 60364-5-51 and IEC 62440

Last Update (16.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® SOLAR H1 BUR

Due to its increased mechanical strength, it is suitable for underground installation in a cable trench with a sand bed, tested using the "Impact-Resistance Test" and the "Crushing-Resistance Test" in accordance with UL 854

Cross-linked insulation and sheath materials promote longevity at high temperatures or at high current load, and provide high dielectric strength and a high short-circuit temperature

IEC certification allows international use of the product in countries in which the IEC standards are applicable

Application range

For unprotected connection of solar modules and inverters in earthed and non-earthed photovoltaic systems according to EN 50618 and IEC 62930

For fixed installation and occasional flexing, if necessary freely hanging

Underground installation in protective cable conduits only with drainage of accumulated water

Underground installation in a cable trench with a sand bed based on VDE 0891-6 and DIN EN 50174-3

Expected service life of 25 years in accordance with EN 50618 and IEC 62930 in case of norm-compliant wiring and operation

Product features

Weather/ UV resistant per EN 50618 as well as ozone resistant per EN 50396;

Transversely watertight "AD8" per IEC 60364-5-51/ HD 60364-5-51, IEC 62440, and EN 50525-2-21

Flame retardant per IEC 60332-1-2, and Dca classified per EU CPR - Construction Product Regulation (EU) No. 305/2011

Halogen-free according to IEC 60754-1 (amount of halogen acid gas),

Low Corrosiveness of combustion gases according to IEC 60754-2 (degree of acidity)

Good notch and abrasion resistance

Tested against burial-related, mechanical UL 854 Tests Impact-Resistance and Crushing-Resistance

Norm references / Approvals

"H1Z2Z2-K" type-certified by TÜV as per EN 50618

"62930 IEC 131" type-certified by TÜV as per IEC 62930

Product Make-up

Fine-wire, tinned-copper conductor

Core insulation made of cross-linked copolymer

Outer sheath made of cross-linked copolymer

Outer sheath colour: black, red or blue

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class-Description: Flexible cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class-Description: Flexible cable

Conductor stranding:

Fine wire according to VDE 0295,
class 5/IEC 60228 class 5

Minimum bending radius:

Occasional flexing: 15xOD
Stationary use: 4xOD (5xOD only where OD >8mm)

Nominal voltage:

AC U_0/U : 1.0/1.0 kV
DC U_0/U : 1.5/1.5 kV
Max. permissible DC operating voltage: 1.8 kV

Test voltage:

AC 6500 V

Current rating:

Im compliance with EN 50618
Acc. to EN 50618, reduction factors for clustered wiring per... HD 60364-5-52

Temperature range:

>Conductor..., max., per EN 60216-1: 120 °C;

Last Update (16.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® SOLAR H1 BUR

- >Conductor..., max., short-circuit/ earth fault (period of max. 5 s): 250 °C;
- >Ambient..., min., stationary use: -40 °C;
- >Ambient..., min., flexible use or during installation: -25 °C;
- >Ambient..., max., in conjunction with EN 60216-1: 90 °C;
- >Ambient..., constant, in conjunction with HD 60364-7-712: 70 °C to 90 °C;
- >Ambient..., ambient temp. related reduction factor 1.00: 60 °C;
- >Ambient..., max., storage: 40 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® SOLAR H1 BUR

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)
Black outer sheath			
38115806	1 X 4	5.6	38.4
38115807	1 X 6	6.2	57.6
38115808	1 X 10	7.4	96
Red outer sheath			
38115813	1 X 4	5.6	38.4
38115814	1 X 6	6.2	57.6
38115815	1 X 10	7.4	96
Blue outer sheath			
38115820	1 X 4	5.6	38.4
38115821	1 X 6	6.2	57.6
38115822	1 X 10	7.4	96