

ÖLFLEX® TRUCK 170 TWIN

ÖLFLEX® TRUCK 170 TWIN - PVC battery cable for commercial vehicles, black-red coloured for batteries , 60V DC, ADR, TÜV, ISO

Info

Battery twin cable

For commercial vehicles

For hazardous materials transportation



Good chemical resistance



UV-resistant

Benefits

Polarity identification is possible without stripping the sheath or external marking (the item designation is always printed on the positive pole). This rules out incorrect connections.

No brushing of cores after stripping and therefore optimum subsequent handling, for example when crimping/contacting
Special ADR approval

Application range

Battery cable between the power source and the end user

For commercial vehicles

Product features

Double-sheathed version, extremely tough, for installation without corrugated tubing

Very strong connection but offering easy separation of the cable by hand

Norm references / Approvals

ADR approval TÜ.EGG.091-04

Product Make-up

Conductor made of bare copper wires

Core insulation: Based on PVC

Special PVC-based outer sheath

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® TRUCK 170 TWIN

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable
Minimum bending radius:	15 x outer diameter
Nominal voltage:	60 V DC
Test voltage:	3000 V AC
Temperature range:	Fixed installation: -40 °C to +85 °C Area of application, Class A

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Details of the clamping force are available upon request, halogen-free.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® TRUCK 170 TWIN

Article number	Number of cores and mm ² per conductor	Outer dimensions, width x height (mm)	Copper index (kg/km)
ÖLFLEX® TRUCK 170 TWIN PVC/PVC			
7027055	PVC/PVC 2 x 6,0	15.2 x 7.1	115.2
7027056	PVC/PVC 2 x 10,0	18.8 x 8.9	192
7027057	PVC/PVC 2 x 16,0	21 x 10	307.2
7027058	PVC/PVC 2 x 25,0	25.6 x 12.3	480
7027059	PVC/PVC 2 x 35,0	28.4 x 13.5	672
7027054	PVC/PVC 2 x 50,0	33 x 16	960
7027052	PVC/PVC 2 x 70,0	39.8 x 18.4	1344