

ÖLFLEX® TRAIN 340 600V

Multi-core cable according to EN 50264-3-2 type MM for high requirements in railway applications

ÖLFLEX® TRAIN 340 600V - Control cable EN 50264-3-2 MM, 0,6/1kV for high requirements in railways/rolling stock
EN 45545: HL1-HL3, NF F 16-101: C/F0

Info

Meets EN 50264-3-2 type MM and
EN 45545-2

High temperature resistance: -50°C up to 120°C

Highly oil- and fuel-resistant



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Mechanical resistance



Oil-resistant



Temperature-resistant

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® TRAIN 340 600V



UV-resistant

Benefits

Good chemical resistance please see Appendix T1

Resistant to mechanical influences in harsh environmental conditions

Extended temperature range

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

Application range

For use in railway vehicles, for fixed installations and applications where limited movement may occur

Suitable for connecting lamps, heating equipment, switchgear, terminal boxes and power supply

Also applicable within oily environments and areas with increased ambient temperature

Product features

Fire behaviour according to EN/IEC:

- Halogen-free acc. to EN 60754-1
- No corrosive gases acc. to EN 60754-2
- No fluorine acc. to EN 60684-2
- No toxic gases acc. to EN 50305
- Low smoke density acc. to EN 61034-2
- Flame-retardant acc. to EN 60332-1-2
- No flame propagation acc. to EN 60332-3-24 / EN 60332-3-25 / EN 50305

Fire behaviour according to NF:

- Toxicity of gases acc. to NF X 70-100
- Low smoke density acc. to NF X 10-702
- No flame propagation acc. to NF C 32-070, Cat. C1 and C2

Chemical properties:

- Oil resistant acc. to EN 50264-3-2
- Fuel resistant acc. to EN 50264-3-2
- Acid resistant acc. to EN 50264-3-2
- Alkali resistant acc. to EN 50264-3-2
- Ozone resistant acc. to EN 50264-3-2/ EN 50305)

Current rating according to EN 50355, appendix A

Norm references / Approvals

EN 50264-3-2 type MM

EN 45545-2 HL1, HL2, HL3

NF F 16-101 - Classification: C / F0
(flame propagation / smoke)

Product Make-up

Tinned-copper strand, fine-wire

Insulation: Electron beam cross-linked Polymer compound EI 109

Colour of insulation: Black with white numbers

Outer sheath: electron beam cross-linked polymer-compound EM 104

Outer sheath colour: Black

ÖLFLEX® TRAIN 340 600V

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	Black with white numbers
Conductor stranding:	Fine-wired/ Finely stranded according to IEC 60228, conductor class 5
Minimum bending radius:	Fixed installation: ≤ 12 mm: 3 x OD > 12 mm: 4 x OD Occasional flexing: ≤ 12 mm: 4 x OD > 12 mm ≤ 20 mm: 5 x OD > 20 mm: 6 x OD (OD = outer diameter)
Nominal voltage:	U ₀ /U AC 0.6/1 kV U _m AC 1.2 kV V ₀ DC 0.9 kV
Test voltage:	3,5 kV AC; 8,4 kV DC
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Fixed installation: -45°C to +120°C (20.000 h) -50°C acc. to GOST 20.57.406-81 Occasional flexing: -35°C to +90°C Short circuit: +200°C (5s)

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® TRAIN 340 600V

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
15340060	2 X 1.0	6.4	19.2	68
15340000	2 X 1.5	7.4	28.8	94.1
15340001	3 X 1.5	7.9	43.2	113.5
15340025	3 G 1.5	7.9	43.2	113.5
15340002	4 X 1.5	8.6	57.6	139.6
15340026	4 G 1.5	8.6	57.6	139.6
15340003	2 X 2.5	8.2	48	127.4
15340004	3 X 2.5	8.7	72	156.9
15340027	3 G 2.5	8.7	72	156.9
15340005	4 X 2.5	9.6	96	195
15340028	4 G 2.5	9.6	96	195
15340006	2 X 4.0	9.6	76.8	178.5
15340007	3 X 4.0	10.2	115.2	222.9
15340008	4 X 4.0	11.4	153.6	284.5
15340009	2 X 6.0	10.8	115.2	244.2
15340010	3 X 6.0	11.5	172.8	308
15340011	4 X 6.0	13.0	230.4	393.4
15340012	2 X 10.0	13.2	192	377.3
15340013	3 X 10.0	14.0	288	479.6
15340014	4 X 10.0	15.4	384	604
15340015	2 X 16.0	15.2	307.2	551.9
15340016	3 X 16.0	16.2	460.8	708
15340017	4 X 16.0	18.2	614.4	916.2
15340018	2 X 25.0	19.0	480	857
15340019	3 X 25.0	20.2	720	1,101.5
15340020	4 X 25.0	22.7	960	1,420.9
15340021	2 X 35.0	21.4	672	1,140.9
15340022	3 X 35.0	23.0	1008	1,488.8
15340023	2 X 50.0	26.2	960	1,626.5
15340024	3 X 50.0	28.0	1440	2,101.1