

## KWB 4099 crimping pliers

KWB 4099: Crimping pliers for pressing non-insulated cable lugs from 4,0-10,0 mm<sup>2</sup>, Crimping profile: W-pressing, ergonomic design



Reliability

### Benefits

- Clearly marked press moulds
- Locking function for faultless pressing
- Handles suit both large and small hands
- Unique mechanism reduces the manual force from 450 N to 250 N
- Tested for a minimum of 80,000 pressings

### Application range

The Miniforce tool for non-insulated connections of 4 - 10 mm<sup>2</sup>  
For non-insulated cable lugs, other connectors and tubular cable lugs KR

### Product features

Emergency release, if the pressing operation needs to be interrupted

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000168 ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000168 ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection
General:	Adjustable crimping pressure
Note:	Crimping profile: W-pressing

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## KWB 4099 crimping pliers

Article number	Article designation	For mm <sup>2</sup>	Weight (kg)	Length (mm)	Pieces / PU
61722130	KWB 4099	4 - 10	0.5	220	1