


V 1311-A pressing pliers, hydraulic

V 1311: Hydraulic Pressing Pliers for cable lugs and butt connectors, 10-400 mm², crimping profile: hexagonal, pressing force: 13 t



Benefits

- Automatic quick feed of pressing dies and mandrels
- Requires low hand force, about 245 N at max. force
- Ergonomic handles
- Pressing head rotates by 180 degrees
- Few tool parts, easy to change

Application range

System 1311 for pressing copper connections of 10 - 400 mm²

Included

- Complete unit, no external pump required
- Supplied with wooden carry box
- Pressing dies and die holders need to be ordered separately

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

On request:

Battery powered tool on request

Note:

Crimping profile: Hexagonal and mandrel
Pressing force: 130 kN (13 t)

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

V 1311-A pressing pliers, hydraulic

Article number	Article designation	For mm ²	Inner die holders	Outer die holders	Weight (kg)	Length (mm)	Pieces / PU
61795925	V 1311-A	10 - 400	V 1316	V 1318	4.9	590	1