

## KNIPEX Ratchet cutter

KNIPEX ratchet shears for conductors with an outer diameter of up to 60 mm, ergonomic design, made in Germany

### Info

Less power required due to very high transmission ratio



### Benefits

One-hand operation through ratchet principle  
High ergonomics thanks to multi-component handles  
Insulated handles allow working under voltage up to 1000V

### Application range

Cuts copper and aluminium cables  
Not suitable for steel wire and wire ropes

### Product features

Precision ground, hardened blades  
Swivel knife can be unlocked in any cutting position with a press of the thumb

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000142 ETIM 5.0 Class-Description: Cable shears
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000142 ETIM 6.0 Class-Description: Cable shears
Certifications:	Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC VDE-tested
Material:	High-grade special tool steel, forged, oil-hardened

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## KNIPEX Ratchet cutter

Article number	Article designation	Cable diameter mm	Weight (kg)	Length (mm)	Pieces / PU
62120524	Ratchet shear KSRI 525	32	0.652	250	-
62120525	Ratchet shear KSRI 628	52	0.835	280	-
Accessories					
61813760	Spare blade KSRI 525	-	-	-	1
61813775	Spare blade KSRI 628	-	-	-	1