









## SKINDICHT® BL-M FKM

SKINDICHT® BL-M, brass bling plug with FKM o-ring to close unused threaded bore holes, mounting with screwdriver



-  Mechanical and plant engineering
-  Oil & Gas
-  Heat-resistant
-  Corrosion-resistant
-  Mechanical resistance
-  Oil-resistant
-  Robust
-  Reliability
-  Temperature-resistant

### Benefits

Withstands temperatures up to +200 °C.

Simple assembly by using a slotted screwdriver.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

Last Update (06.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINDICHT® BL-M FKM

### Application range

For closing an unoccupied metric threaded hole on the housing.  
Withstands high chemical and mechanical stress.

### Product features

Assembling with screwdriver

### Product Make-up

Metric connection thread acc. to DIN EN 60423  
Basis for technical information DIN IEC 62444

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class-Description: Plug for cable screw gland
Material:	Body: nickel-plated brass O-Ring: FKM
Protection rating:	IP66 IP 68 - 10 bar
Temperature range:	-20°C to +200°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® BL-M FKM**

Article number	Article designation / size	Overall length C mm	Thread length D mm	Outer Ø (mm)	Pieces / PU
52123100	M12x1,5	7.5	5	14.0	50
52123110	M16x1,5	8.0	5	18.0	50
52123120	M20x1,5	9.5	6	22.0	50
52123130	M25x1,5	11.0	7	28.0	50
52123140	M32x1,5	12.0	8	35.0	25
52123150	M40x1,5	13.0	9	44.0	25
52123160	M50x1,5	15.0	9	54.0	5
52123170	M63x1,5	16.0	10	70.0	5
lead free brass version					
52123100LF	M12x1,5	7.5	5	14.0	50
52123110LF	M16x1,5	8.0	5	18.0	50
52123120LF	M20x1,5	9.5	6	22.0	50
52123130LF	M25x1,5	11.0	7	28.0	50
52123140LF	M32x1,5	12.0	8	35.0	25
52123150LF	M40x1,5	13.0	9	44.0	25
52123160LF	M50x1,5	15.0	9	54.0	5
52123170LF	M63x1,5	16.0	10	70.0	5

Last Update (06.05.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16