# 0080000 DATA SHEET

valid from: 08.08.2023

# ÖLFLEX® HEAT 205 SC



## **Application**

ÖLFLEX® HEAT 205 SC are heat resistant insulated strands. Besides having excellent mechanical and physical properties. ÖLFLEX® HEAT 205 SC strands are characterized by very good electrical values, outstanding resistance against oil, weather and UV-radiation, as well as having high elasticity and tensile strength of the insulation material.

ÖLFLEX® HEAT 205 SC strands are resistant against the action of water, acids, alkalis, solvents, synthetic liquids and oils.

### Design

Conductor compacted fine wire strands of non-porous tinned copper wires

according to IEC 60228 resp. EN 60228, Class 5

Insulation stress-crack resistant FEP according to type 6YI1 (VDE 0207 part 6)

Core identification code Available core colours:

 $\mathsf{GN}\text{-}\mathsf{YE} / \mathsf{BK} / \mathsf{BU} / \mathsf{BN} / \mathsf{BG} / \mathsf{YE} / \mathsf{GN} / \mathsf{VT} / \mathsf{PK} / \mathsf{OG} / \mathsf{RD} / \mathsf{WH} / \mathsf{GR}$ 

#### Electrical properties at 20 °C

Nominal voltage  $U_0/U$ : 300/500 V Test voltage 2500 V AC

#### Mechanical and thermal properties

Minimum bending radius occasional flexing: 10 x outer diameter

fixed installation: 4 x outer diameter

Temperature range occasional flexing: -100 °C up to +205 °C

fixed installation: -100 °C up to +205 °C

Flammability flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2

General requirements These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive)

**Environmental information** These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: ALTE / PDC Document: DB0080000EN
Released: HESC / PDC Version: 06
Page 1 of 1