

SKINDICHT® MR-M ATEX

SKINDICHT® MR-M ATEX, reducers, enables the use of cable glands with smaller connection threads than the existing threaded holes



Benefits

Enables the use of cable glands with smaller connection threads than the existing threaded holes
With guide notch for O-ring
Assembling with a wrench

Application range

Equipment group II / Category 2G+1D
Devices, machines and apparatus
For mobile applications in offshore and marine industries
Chemical and petrochemical industry

Norm references / Approvals

DIN EN 60079-0
DIN EN 60079-7
DIN EN 60079-31

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441
ETIM 6.0 Class-Description: Cable screw gland

Certifications:

CE 0637 Ex II 2G
Ex eb IIC
Ex II 1D Ex ta IIIC
IECEx IBE 13.0028X

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® MR-M ATEX

| | |
|--------------------|--|
| Material: | Body: nickel-plated brass O-ring: NBR |
| Temperature range: | -30°C to +90°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® MR-M ATEX

| Article number | Thread, male M1 | Thread, female M2 | Overall height (mm) | SW wrench size mm | Thread length D mm | Outer Ø (mm) | Pieces / PU |
|----------------------|-----------------|-------------------|---------------------|-------------------|--------------------|--------------|-------------|
| SKINDICHT® MR-M ATEX | | | | | | | |
| 52104570 | 16 x 1.5 | 12 x 1.5 | 10.5 | 17 | 5 | 19.0 | 50 |
| 52104571 | 20 x 1.5 | 16 x 1.5 | 13 | 22 | 6 | 24.5 | 50 |
| 52104572 | 25 x 1.5 | 20 x 1.5 | 15 | 27 | 7 | 30.1 | 25 |
| 52104573 | 32 x 1.5 | 25 x 1.5 | 16.5 | 34 | 8 | 37.2 | 25 |
| 52104574 | 40 x 1.5 | 32 x 1.5 | 16.5 | 41 | 8 | 45.6 | 10 |
| 52104575 | 50 x 1.5 | 40 x 1.5 | 19.5 | 50 | 10 | 55.3 | 5 |
| 52104576 | 63 x 1.5 | 50 x 1.5 | 18.5 | 65 | 8.5 | 71.3 | 5 |

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16