

SKINDICHT® SE-M without E+D

SKINDICHT® SE-M without E+D, angular cable outlet for missing connection thread and high mechanical load, can be combined



Corrosion-resistant



Mechanical resistance



Space requirement



Connector with standard housing unit



Temperature-resistant

Benefits

Combination of different conduit glands is possible

Corrosion-resistant

Easy to install

Completely safe cable entry

Low overall height

Application range

The flange angle gland can be combined with all glands (including O-ring) e.g. strain relief, bending protection and conduit glands

For high mechanical stress

When no connection thread is provided

Product Make-up

M20 x 1.5 - M25 x 1.5 with 2 screw holes

M32 x 1.5 with 4 screw holes

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SE-M without E+D

Note

The protection class is dependent on the combination with the various special glands. The minimum standard is IP 55.
For combination with other SKINDICHT® or SKINTOP® cable glands, we propose our SKINDICHT® SE-M without incised sealing ring (E) and compression screw (D)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Material:	Body: zinc die-casting, grey, hammer tone finish O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SE-M without E+D

Article number	Article designation / size	Height (mm)	Overall width (mm)	Length (mm)	PU
SKINDICHT® SE-M without E+D					
52108001	M 20 x 1,5	31.0	42.0	42.0	10
52108011	M 25 x 1,5	40.0	60.0	60.0	5
52108021	M 32 x 1,5	51.5	66.0	76.0	1