SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R, resistant stainless steel cable gland with smooth surfaces for use in product zone

Info

New: Available up to size M40x1,5
Ideal for hygienic critical areas - resistant, edge-free, robust and reliable
No gaps, voids or outer lying thread - so no risk of contamination of food machines, facilities or components







- Food & Beverage
- Good chemical resistance
- Wide clamping range
- Mechanical resistance
- Temperature-resistant

Benefits

Hygienic Design for ideal cleaning results
Smooth surfaces and no edges prevent the accumulation of fluids and formation of micro-organisms

Application range

Food machinery, equipment and components
For use in **product zone**
Pharmaceutical industry

Last Update (30.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

Norm references / Approvals

EHEDG (TYPE EL Class I AUX)
Hygienic design for machinery and components
ECOLAB®
Industry standard in the field of professional cleaning and disinfection in the food and beverage industry
FDA 21 CFR 177.2600
Special sealing element for food and beverage industry in North America
DIN EN 1672-2
Guideline for the design of machinery
DIN EN ISO 14159
Security of machinery – Hygienic requirements for the design of machinery
NSF/ANSI 169
Hygienic design for machinery and components

Product Make-up

Material and shape provide an easy and safe cleaning
By the blue coloring of the sealing material clearly distinguishable from foodstuffs
One complete assembly is easily mounted from the outside
Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Note

Installation wrench for very high packing density on request

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Certifications:	UL approval for M32x1,5 and M40x1,5 pending
Material:	Body: stainless steel - V4A (1.4404 / 316L) Insert: polyamide Sealing: special elastomer
Protection rating:	IP 68 - 10 bar IP 69 NEMA Type 1, 2, 4x, 6, 12
Temperature range:	-20°C to +100°C

Note

Other sizes are available upon request.
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R


Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
SKINTOP® HYGIENIC						
53105100	M 12 x 1,5	4 - 6	16	38.4	6.5	5
53105110	M 16 x 1,5	6.5 - 9	20	41.4	7	5
53105120	M 20 x 1,5	9 - 12	24	46.4	8	5
53105130	M 25 x 1,5	11.5 - 15.5	29	48.9	8	5
SKINTOP® HYGIENIC-R						
53105200	M 12 x 1,5	3 - 4.5	16	38.4	6.5	5
53105210	M 16 x 1,5	4.5 - 7	20	41.4	7	5
53105220	M 20 x 1,5	7 - 10	24	46.4	8	5
53105230	M 25 x 1,5	9 - 12.5	29	48.9	8	5

Last Update (30.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R







©2023 Lapp Group - Technical changes reserved