


ETHERLINE® Cat.6A

Ethernet cable Category 6_A, Class E_A for fixed installation - verified up to 500 MHz

Industrial Ethernet cable Cat.6A for fixed installation
halogenfree, PVC or PUR outer sheath, design 4x2xAWG22/1

Info

CPR: Article number choice under www.lappkabel.com/cpr
For PROFINET applications with 4 pairs
CAT.6_A qualified for 10Gbit/s



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Interference signals



UV-resistant

Benefits

Can be used in dry or damp rooms
Screened against interference
Can be used for Industrial Ethernet in harsh industrial environments
4pair: 100Mbit/s up to 10 Gbit/s for Industrial Ethernet

Application range

for industrial secondary and tertiary cabling according to EN 50173-3
ISO/IEC 24702
Wiring of machines, tools, devices, appliances and control cabinets

Last Update (26.05.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ETHERLINE® Cat.6A

suitable for EtherCAT and EtherNet/IP applications

Product features

PUR outer sheath is highly resistant to mineral oils and abrasion

Robust, halogen-free outer sheath

The oil-resistant PVC sheath enables usage in industrial environments

High-quality, double screening ensures high transmission reliability in areas with electromagnetic interference

Product Make-up

Solid bare copper wire AWG22

Core insulation made of polyethylene (PE)

S/FTP: copper braid as overall screening and pair screening with aluminium compound foil

Colour: green (based on RAL 6018)

Technical Data

Classification:	ETIM 5.0/6.0 Class-ID: EC000830 ETIM 5.0/6.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Peak operating voltage:	(not for power applications) 125 V
Minimum bending radius:	Fixed installation: 10 x outer diameter
Characteristic impedance:	100 Ω \pm 5 Ohm (> 1 MHz)
Temperature range:	Cable with PUR sheath Fixed installation: -40 °C to +80 °C Cable, halogen-free outer sheath Fixed installation: -25 °C to +80 °C Cable with PVC sheath Fixed installation: -30 °C to +80 °C

Note

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

PROFINET® is a registered trademark of the PNO (PROFIBUS user organisation)

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ETHERLINE® Cat.6A

Article number	Article designation	Number of pairs and AWG per conductor	Core diameter in mm	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
Halogen-free jacket						
2170466	ETHERLINE® Cat.6 _A H	4 x 2 x AWG22/1	1.5	8.7	53	99
PUR outer sheath, halogen-free						
2170465	ETHERLINE® CAT.6 _A P	4 x 2 x AWG22/1	1.5	8.7	53	91
PVC outer sheath						
2170464	ETHERLINE® Cat.6 _A Y	4 x 2 x AWG22/1	1.5	8.7	53	98

Last Update (26.05.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

ETHERLINE® Cat.6A

