


ETHERLINE® PN Cat.6A FLEX







Flexible use

Industrial Ethernet cable Cat.6A for flexible use, 4 pairs, PVC or FRNC outer sheath with UL-approval, 4x2xAWG23/7

Info

For PROFINET applications with 4 pairs
 CAT.6A qualified for 10Gbit/s



-  Supplementary automation components from Lapp
-  Mechanical and plant engineering
-  Suitable for outdoor use
-  Flame-retardant
-  Interference signals
-  UV-resistant

Benefits

- Can be used in dry or damp rooms
- Screened against interference
- Can be used for Industrial Ethernet in harsh industrial environments
- 4pair: 100Mbit/s up to 10 Gbit/s for Industrial Ethernet

Application range

for industrial secondary and tertiary cabling according to EN 50173-3
 ISO/IEC 24702

ETHERLINE® PN Cat.6A FLEX

Wiring of machines, tools, devices, appliances and control cabinets
 suitable for EtherCAT and EtherNet/IP applications
 For flexible applications
 (7-wire stranded conductor)

Product features

CAT.6_A for flexible application, qualified for 10Gbit/s
 Meets the requirements according to CAT.6A, ISO/IEC 11801 and EN 50173
 High-quality, double screening ensures high transmission reliability in areas with electromagnetic interference
 The oil-resistant PVC sheath enables usage in industrial environments

Norm references / Approvals

UL approvals see data sheet
 ETHERLINE® PN Cat.6A Y FLEX: ECOLAB®
 Industry standard for innovation and efficiency in the field of professional cleaning and disinfection

Product Make-up

7-wire tinned stranded copper conductor
 Core insulation: PE
 S/FTP: copper braid as overall screening and pair screening with aluminium compound foil
 PVC or FRNC jacket material
 Colour: green (based on RAL 6018)

Technical Data

Classification ETIM 5:	ETIM 5.0/6.0 Class-ID: EC000830 ETIM 5.0/6.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Peak operating voltage:	(not for power applications) 125 V
Minimum bending radius:	Flexing: 15 x outer diameter Fixed installation: 8 x outer diameter
Characteristic impedance:	nom. 100 Ω acc. to IEC 61156-5
Temperature range:	cable halogenfree compound Fixed installation: -25 °C to +80 °C Occasional flexing: -10 °C to +80 °C cable with PVC jacket Fixed installation: -40 °C to +80 °C Occasional flexing: -10 °C to +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

PROFINET® is a registered trademark of the PNO (PROFIBUS user organisation)

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ETHERLINE® PN Cat.6A FLEX

Article number	Article designation	Number of pairs and AWG per conductor	Core diameter in mm	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
PVC outer sheath						
2170930	ETHERLINE PN Cat.6 _A Y FLEX	4 x 2 x AWG23/7	1.5	8.8	48	92
FRNC outer sheath						
2170931	ETHERLINE PN Cat.6 _A FRNC FLEX	4 x 2 x AWG23/7	1.5	8.8	48	87

Last Update (01.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

ETHERLINE® PN Cat.6A FLEX

