

## UNITRONIC® LAN FLEX

Data cable for patchcable applications

The LAN cable has good flexibility and can be installed easily in restricted spaces. The cable is suitable for connection in control cabinets.

### Info

Only for patch cable applications  
(max. 60 m)



Halogen-free



Interference signals

### Benefits

For directly connecting two electric components  
Easy to assemble

### Application range

Indoor applications  
LAN connections  
Control cabinet wiring

### Product features

Good flexibility - easy installation with tight space requirements  
Flame retardant acc. to IEC 60332-1-2  
2170139: flame retardant acc. to IEC 60332-1-2 and IEC 60332-3-24

### Product Make-up

F/UTP: foil screening as overall screening  
SF/UTP: braid of tinned copper wire and plastic laminated aluminum foil as overall screening  
S/FTP: copper braid as overall screening and pair screening with aluminium compound foil  
outer sheath either as PVC or LSZH (color grey RAL 7035)

### Technical Data

Last Update (10.05.2024)  
©2024 Lapp Group - Technical changes reserved  
Product Management [www.lappkabel.de](http://www.lappkabel.de)  
You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16

## UNITRONIC® LAN FLEX

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Minimum bending radius:	Fixed installation: 4 x outer diameter during installation: 8 x outer diameter
Mean characteristic Impedance:	100 $\Omega$ $\pm$ 15%
Temperature range:	Fixed installation: -20 °C to +60 °C Flexing: 0 °C to +50 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: Coil 100 m; Drum (500; 1000) m

Detailed data sheets are available upon request. Please specify the type/dimensions of the required cable.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**UNITRONIC® LAN FLEX**

Article number	Article designation	Number of pairs and AWG per conductor	Outer diameter mm	Copper index (kg/km)	Weight (kg/km)
PVC versions					
2170127	UNITRONIC LAN 200 F/UTP Cat.5e FLEX	4 x 2 x AWG26/7	5.6	13	28
2170129	UNITRONIC LAN 200 SF/UTP Cat.5e FLEX	4 x 2 x AWG26/7	6.0	22	36
2170144	UNITRONIC LAN 600 S/FTP Cat.7 Y FLEX	4 x 2 x AWG26/7	6.5	22	39
Halogen-free versions					
2170172	UNITRONIC LAN 200 F/UTP Cat.5eLSZH FLEX	4 x 2 x AWG26/7	5.6	13	28
2170139	UNITRONIC LAN 200 SF/UTP Cat.5eLSZH FLEX	4 x 2 x AWG26/7	6.0	22	36
2170142	UNITRONIC LAN 600 S/FTP Cat.7 LSZH Flex	4 x 2 x AWG26/7	6.2	21	40

Last Update (10.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16