

## EPIC® DATA CAN M12/M12

M12 control cabinet feed-through, shielded for CAN/DeviceNet/ S/A cabling

sensor/actuator control cabinet feed through with bipolar/screw mounting (A-coded)



DeviceNet CANopen



Supplementary automation components from Lapp



Mechanical and plant engineering



Interference signals



Waterproof

### Benefits

M12 connector on both sides

Plug & Play for flexible connection solutions

### Product features

For CANopen/DeviceNet applications

For sensor/actuator cabling

Bipolar/screw mounting

### Product Make-up

5-pin control cabinet feed-through, M12 A-coded

M12 plug on M12 socket

Screened version

### Technical Data

Material:

Contact: CuZn

Contact surface: Au (gold)

Contact carrier: PA 66

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**EPIC® DATA CAN M12/M12**

	Knurl: Nickel-plated brass
	Sealing: FKM
Protection rating:	IP 67
Ambient temperature (operation):	Plug/socket -25°C to +85°C
Coding:	A - Standard (CANopen/DeviceNet/CC-Link)
Rated current (A):	4 A

**Note**

DeviceNet is a registered trademark of ODVA

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® DATA CAN M12/M12**

Article number	Article designation	Number of pins	Rated voltage (V)	PU
Control cabinet feed through				
22262020	AB-C5-DSI-M12MS-M12FS-M16-SH	5	24	1