

UNITRONIC® BUS PB FD P COMBI

Highly flexible, halogenfree PROFIBUS HYBRID cables

Bus cable for PROFIBUS-DP, -FMS and FIP. HYBRID: Data transmission and power supply. Temperature range from -40°C bis +80°C

LAPP KABEL STUIGART UNITRONIC® BUS PB FD P COMBI 



Supplementary automation components from Lapp



Mechanical and plant engineering



Power chain

Benefits

For use where the combination of a halogen-free outer sheath with properties similar to PUR and enhanced flame-retardance is required

For highly flexible applications (power chains, moving machine parts)

Cables can be used for PROFIBUS-DP as well as PROFIBUS-FMS and FIP

Application range

PROFIBUS DP (in accordance with DIN 19245 and EN 50170, e.g. for SIEMENS SIMATIC® NET, also suitable for FIP - Factory Instrumentation Protocol).

Product features

HYBRID: cable for data transmission + power supply

Flame-retardant according IEC 60332-1-2

Product Make-up

Fine-wire, bare copper strand

1x2x0.64: red, green

3x1.0 (AWG18): green/yellow, black, blue

Core insulation: PE

Tin-plated copper wire braiding

Outer sheath: PUR, violet (RAL 4001)

Last Update (04.01.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® BUS PB FD P COMBI

Technical Data

| | |
|---------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable |
| Mutual capacitance: | (800 Hz): max. 30 nF/km |
| Peak operating voltage: | (not for power applications) 100 V |
| Test voltage: | Core/core: 600 V |
| Characteristic impedance: | 150 ± 15 Ohm |
| Temperature range: | Flexing: -5 °C to +50 °C Fixed installation: -40 °C to +80 °C |

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

SIMATIC® is a registered trademark of SIEMENS AG. FIP is a registered trademark of World FIP

Lapp Kabel is a member of the PROFIBUS user organisation (PNO)

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UNITRONIC® BUS PB FD P COMBI

| Article number | Article designation | Number of pairs and conductor diameter (mm) | Outer diameter [mm] | Copper index (kg/km) | Weight (kg/km) |
|------------------------------|------------------------------|---|---------------------|----------------------|----------------|
| UNITRONIC® BUS PB FD P COMBI | | | | | |
| 2170227 | UNITRONIC® BUS PB FD P COMBI | 1 x 2 x 0.64 Ø + 3 x 1.0 mm ² | 10.1 | 59 | 125 |

Last Update (04.01.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16