

## UNITRONIC® ROBUST C (TP)

Halogen-free data transmission cable with colour code acc. to DIN 47100 - resistant to a wide range of chemical media

UNITRONIC® ROBUST C (TP): Screened low-freq data cable Twisted pairs Biopetroleum/ cleaner/ hotwater/ hydraulic fluid resistance Outdoor Food Beverage Composting

### Info

Excellent weather resistance

Good chemical resistance please see Appendix T1



Food & Beverage



Suitable for outdoor use



Good chemical resistance



Halogen-free



Cold-resistant



UV-resistant

### Benefits

Outstanding weather, ozone and UV resistance together with the wide temperature range enable versatile use for indoor and outdoor applications

Resistant to contact with organic oils and the related emulsions as well as a multitude of plant, animal or synthetic-based greases and waxes

Good resistance to ammonia compounds and bio-gases

Good resistance to cold and hot water as well as water-soluble cleaning and cooling agents

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## UNITRONIC® ROBUST C (TP)

Well-suited to steam cleaning

### Application range

Machine tool building, medical technology, laundries, car washing equipment, chemical industry, composting plants, sewage works  
Food and beverage industry, especially for production and processing equipment of milk and meat products  
For data processing, measurement and control engineering, safety related systems and as electronics cable  
For indoor and outdoor use

### Product features

Good chemical resistance to ester-based hydraulic fluids  
Ozone, UV and weather-resistant according to EN 50396 and HD 605 S2  
Halogen-free as per IEC 60754-1, Low corrosivity/ acidity of combustion gases per IEC 60754-2, Low toxicity of comb. gases per EN 50305  
Low smoke density according to IEC 61034-2

### Norm references / Approvals

Based on VDE 0812  
Certified resistance to disinfection and cleaning solutions used in food and beverage industry

### Product Make-up

Fine-wire/multi-wire (0.34 mm<sup>2</sup>) strand made of bare copper wires  
Core insulation made of special halogen-free compound  
TP structure  
Tinned-copper braiding  
Outer sheath made of special TPE  
Outer sheath colour: black (RAL 9005)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000830 ETIM 5.0 Class-Description: Data cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000830 ETIM 6.0 Class-Description: Data cable
Core identification code:	DIN 47100 without colour repetition, refer to Appendix T9
Mutual capacitance:	C/C approx. 60 nF/km C/S approx. 100 nF/km
Specific insulation resistance:	> 20 GOhm x cm
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Stranded, fine-wire 0.34 mm <sup>2</sup> : 7-wire
Torsion movement in WTG:	TW-0 & TW-2, refer to Appendix T0
Minimum bending radius:	Occasional flexing: 10 x outer diameter Fixed installation: 4 x outer diameter
Test voltage:	At 0.14 mm <sup>2</sup> : 1200 V
Temperature range:	Occasional flexing: -40 °C to +90 °C Fixed installation: -50 °C to +90 °C

### Note

Last Update (23.04.2024)  
©2024 Lapp Group - Technical changes reserved  
Product Management [www.lappkabel.de](http://www.lappkabel.de)  
You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16

## UNITRONIC® ROBUST C (TP)

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil  $\leq 30$  kg or  $\leq 250$  m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

# UNITRONIC® ROBUST C (TP)

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
UNITRONIC® ROBUST C (TP)				
1032100	2 x 2 x 0.14	5.3	16.1	31
1032101	3 x 2 x 0.14	5.8	19	38
1032102	4 x 2 x 0.14	6.2	23.1	46
1032103	5 x 2 x 0.14	6.4	27.2	54
1032104	6 x 2 x 0.14	7.1	31.3	63
1032105	8 x 2 x 0.14	8.2	43.4	90
1032106	10 x 2 x 0.14	8.7	50.9	93
1032107	12 x 2 x 0.14	8.9	56.6	102
1032108	2 x 2 x 0.25	6.3	22.7	43
1032109	3 x 2 x 0.25	7.1	28.9	56
1032110	4 x 2 x 0.25	7.6	38.3	72
1032111	5 x 2 x 0.25	7.9	45.1	85
1032112	6 x 2 x 0.25	8.5	48.7	96
1032113	8 x 2 x 0.25	10.3	64.3	135
1032114	2 x 2 x 0.34	7.1	27.6	56
1032115	3 x 2 x 0.34	7.8	38.8	74
1032116	4 x 2 x 0.34	8.4	47.5	90
1032117	5 x 2 x 0.34	8.8	58.2	110
1032118	1 x 2 x 0.5	5.6	20.1	37
1032119	2 x 2 x 0.5	7.9	40.3	72
1032120	3 x 2 x 0.5	8.7	51.7	91
1032121	4 x 2 x 0.5	9.4	64.1	112
1032122	5 x 2 x 0.5	10.3	76.6	141
1032123	6 x 2 x 0.5	11.1	91.7	170
1032124	8 x 2 x 0.5	13.1	123.2	238
1032125	10 x 2 x 0.5	14.5	146.4	247
1032126	2 x 2 x 0.75	8.5	48.4	84
1032127	3 x 2 x 0.75	9.4	68.9	114
1032128	4 x 2 x 0.75	10.7	86.2	149
1032129	6 x 2 x 0.75	12.1	131.9	225
1032130	8 x 2 x 0.75	14.7	168.2	315
1032131	2 x 2 x 1.0	9	64.1	98
1032132	3 x 2 x 1.0	10.4	83.5	135

**UNITRONIC® ROBUST C (TP)**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1032133	4 x 2 x 1.0	11.3	105.7	168