

## UNITRONIC® SENSOR M8

M8 plug/socket on free conductor end

Sensor/actuator connecting cable 3-, 4-pin, M8 connector/M8 socket on free cable end, A-coded, PUR halogen-free, IP65/IP67/IP68, LED, suitable for power chains

### Info

Other types are available at  
[www.lappgroup.com/assemblyfinder](http://www.lappgroup.com/assemblyfinder)  
or on request



Supplementary automation components from Lapp



Mechanical and plant engineering



Assembly time



Space requirement



Power chain



UV-resistant



Waterproof

### Benefits

Cost-efficient due to quick and easy installation

Space-saving due to compact dimensions.

Fast and easy error tracking

Gold-plated contacts for low transfer resistance

Last Update (04.01.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## UNITRONIC® SENSOR M8

### Application range

For increased mechanical stress and harsh operating conditions

### Product features

UV-resistant  
Good resistance to oils and chemicals  
PWIS and PVC free  
Suitable for drag chains  
Including tag carrier

### Norm references / Approvals

Halogenfree according to DIN VDE 0472  
UL File Number: E249137  
Flame-retardant according to UL 1581 FT-2

### Product Make-up

Core cross section: 0.25 mm<sup>2</sup>  
Colour-code:  
3-pin: bn (1), bu (3), bk (4)  
4-pin: bn (1), wh (2), bu (3), bk (4)  
Outer sheath: PUR, black

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001855 ETIM 5.0 Class-Description: Sensor-actuator patch cord
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001855 ETIM 6.0 Class-Description: Sensor-actuator patch cord
Material:	Contact: CuSn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: TPU, flame-retardant, self-extinguishing
Minimum bending radius:	Fixed installation: 5 x outer diameter Flexing: 10 x outer diameter
Protection rating:	IP65/IP67/IP68
Ambient temperature (operation):	Plug/socket -25 °C to +90 °C Fixed installation -40 °C to +80 °C Flexing -25 °C to +80 °C
Coding:	A-standard
Rated current (A):	4 A

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UL certifications can be found in the data sheet.

**UNITRONIC® SENSOR M8**

Article number	Article designation	Number of pins	Length (m)	Design	LED	Rated voltage (V)	PU
22260204	AB-C3-M8MS-2,0PUR	3	2	straight	no	60	1
22260205	AB-C3-M8MS-5,0PUR	3	5	straight	no	60	1
22260218	AB-C3-M8MS-10,0PUR	3	10	straight	no	60	1
22260053	AB-C3-M8MA-2,0PUR	3	2	angled	no	60	1
22260987	AB-C3-M8MA-5,0PUR	3	5	angled	no	60	1
22260055	AB-C3-M8MA-10,0PUR	3	10	angled	no	60	1
Socket							
22260202	AB-C3-2,0PUR-M8FS	3	2	straight	no	60	1
22260200	AB-C3-5,0PUR-M8FS	3	5	straight	no	60	1
22260219	AB-C3-10,0PUR-M8FS	3	10	straight	no	60	1
22260203	AB-C3-2,0PUR-M8FA	3	2	angled	no	60	1
22260201	AB-C3-5,0PUR-M8FA	3	5	angled	no	60	1
22260220	AB-C3-10,0PUR-M8FA	3	10	angled	no	60	1
22260275	AB-C3-2,0PUR-M8FA-2L	3	2	angled	2 LEDs	24	1
22260276	AB-C3-5,0PUR-M8FA-2L	3	5	angled	2 LEDs	24	1
22260277	AB-C3-10,0PUR-M8FA-2L	3	10	angled	2 LEDs	24	1
22260300	AB-C4-M8MS-2,0PUR	4	2	straight	no	30	1
22260308	AB-C4-M8MS-5,0PUR	4	5	straight	no	30	1
22260318	AB-C4-M8MS-10,0PUR	4	10	straight	no	30	1
22260056	AB-	4	2	angled	no	30	1

Last Update (04.01.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**UNITRONIC® SENSOR M8**

Article number	Article designation	Number of pins	Length (m)	Design	LED	Rated voltage (V)	PU
	C4-M8MA-2,0PUR						
22260057	AB-C4-M8MA-5,0PUR	4	5	angled	no	30	1
22260058	AB-C4-M8MA-10,0PUR	4	10	angled	no	30	1
Socket							
22260309	AB-C4- 2,0PUR-M8FS	4	2	straight	no	30	1
22260310	AB-C4- 5,0PUR-M8FS	4	5	straight	no	30	1
22260317	AB-C4-10,0PUR-M8FS	4	10	straight	no	30	1
22260311	AB-C4- 2,0PUR-M8FA	4	2	angled	no	30	1
22260312	AB-C4- 5,0PUR-M8FA	4	5	angled	no	30	1
22260319	AB-C4-10,0PUR-M8FA	4	10	angled	no	30	1

Last Update (04.01.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16

## UNITRONIC® SENSOR M8

