

UNITRONIC® SENSOR M12-M12

M12 plug on M12 socket

Sensor/Actuator-cable, connecting cable 3-,4-,5-,8-pin, M12 on M12/ on free conductor end, A-codiert, PUR halogenfree, IP65/IP67/IP68, suitable for drag chains

Info

Other types are available at
www.lappgroup.com/assemblyfinder
or on request



Supplementary automation components from Lapp



Mechanical and plant engineering



Space requirement



Power chain



Waterproof

Benefits

Cost-saving due to quick and easy installation
Space-saving due to compact dimensions.
Fast and easy error tracking
Integrated vibration protection (mechanical lock-in)
Gold-plated contacts for low transfer resistance

Application range

For increased mechanical stress and harsh operating conditions

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12-M12

Product features

UV-resistant
Good resistance to oils and chemicals
PWIS and PVC free
Suitable for drag chains
Including tag carrier

Norm references / Approvals

Halogenfree according to DIN VDE 0472
UL File Number: E249137
Flame-retardant according to UL 1581 FT-2

Product Make-up

wire cross-section: 0,34 mm²
(8-pin: 0,25 mm²)
Colour-code:
3-pin: bn (1), bu (3), bk (4)
4-pin: bn (1), wh (2), bu (3), bk (4)
5-pin: bn (1), wh (2), bu (3), bk (4), gn/ye (5)
8-pin: wh (1), bn (2), gn (3), ye (4), gy (5), pk (6), bu (7), rd (8)
Outer sheath: PUR, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001855 ETIM 5.0 Class-Description: Sensor-actuator patch cord
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001855 ETIM 6.0 Class-Description: Sensor-actuator patch cord
Material:	Contact: CuSn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: TPU, flame-retardant, self-extinguishing
Minimum bending radius:	Fixed installation: 5 x outer diameter Flexing: 10 x outer diameter
Protection rating:	IP65/IP67
Ambient temperature (operation):	Plug/socket -25 °C to +90 °C Fixed installation -40 °C to +80 °C Flexing -25 °C to +80 °C
Coding:	A-standard
Rated current (A):	4 A 2 A (8-pin)

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: inclusive of copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UL certifications can be found in the data sheet.

UNITRONIC® SENSOR M12-M12

Article number	Article designation	Length (m)	Design	LED	Rated voltage (V)	PU
22260233	AB-C3-M12MS-0,3PUR-M12FS	0.3	straight-straight	no	250	1
22260234	AB-C3-M12MS-0,6PUR-M12FS	0.6	straight-straight	no	250	1
22260235	AB-C3-M12MS-1,0PUR-M12FS	1	straight-straight	no	250	1
22260236	AB-C3-M12MS-2,0PUR-M12FS	2	straight-straight	no	250	1
22260237	AB-C3-M12MS-0,3PUR-M12FA	0.3	straight-angled	no	250	1
22260238	AB-C3-M12MS-0,6PUR-M12FA	0.6	straight-angled	no	250	1
22260239	AB-C3-M12MS-1,0PUR-M12FA	1	straight-angled	no	250	1
22260240	AB-C3-M12MS-2,0PUR-M12FA	2	straight-angled	no	250	1
22260261	AB-C3-M12MS-0,3PUR-M12FA-2L	0.3	straight-angled	2 LEDs	24	1
22260262	AB-C3-M12MS-0,6PUR-M12FA-2L	0.6	straight-angled	2 LEDs	24	1
22260263	AB-C3-M12MS-1,0PUR-M12FA-2L	1	straight-angled	2 LEDs	24	1
22260264	AB-C3-M12MS-2,0PUR-M12FA-2L	2	straight-angled	2 LEDs	24	1
4-pin						
22260328	AB-C4-M12MS- 0,3PUR-M12FS	0.3	straight-straight	no	250	1
22260329	AB-C4-M12MS- 0,6PUR-M12FS	0.6	straight-straight	no	250	1
22260330	AB-C4-M12MS- 1,0PUR-M12FS	1	straight-straight	no	250	1
22260331	AB-C4-M12MS- 2,0PUR-M12FS	2	straight-straight	no	250	1
22260332	AB-C4-M12MS- 0,3PUR-M12FA	0.3	straight-angled	no	250	1
22260333	AB-C4-M12MS- 0,6PUR-M12FA	0.6	straight-angled	no	250	1
22260334	AB-C4-M12MS-1,0PUR-M12FA	1	straight-angled	no	250	1

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

UNITRONIC® SENSOR M12-M12

Article number	Article designation	Length (m)	Design	LED	Rated voltage (V)	PU
22260335	AB-C4-M12MS-2,0PUR-M12FA	2	straight-angled	no	250	1
22260336	AB-C4-M12MS-0,3PUR-M12FA-3L	0.3	straight-angled	3 LEDs	24	1
22260337	AB-C4-M12MS-0,6PUR-M12FA-3L	0.6	straight-angled	3 LEDs	24	1
22260338	AB-C4-M12MS-1,0PUR-M12FA-3L	1	straight-angled	3 LEDs	24	1
22260339	AB-C4-M12MS-2,0PUR-M12FA-3L	2	straight-angled	3 LEDs	24	1
22260304	AB-C4-M12MA-0,3PUR-M12FS	0.3	angled-straight	no	250	1
22260305	AB-C4-M12MA-0,6PUR-M12FS	0.6	angled-straight	no	250	1
22260306	AB-C4-M12MA-1,0PUR-M12FS	1	angled-straight	no	250	1
22260307	AB-C4-M12MA-2,0PUR-M12FS	2	angled-straight	no	250	1
5-pin						
22260410	AB-C5-M12MS-0,3PUR-M12FS	0.3	straight-straight	no	60	1
22260411	AB-C5-M12MS-0,6PUR-M12FS	0.6	straight-straight	no	60	1
22260412	AB-C5-M12MS-1,0PUR-M12FS	1	straight-straight	no	60	1
22260413	AB-C5-M12MS-2,0PUR-M12FS	2	straight-straight	no	60	1
22260063	AB-C5-M12MS-0,3PUR-M12FA	0.3	straight-angled	no	60	1
22260064	AB-C5-M12MS-0,6PUR-M12FA	0.6	straight-angled	no	60	1
22260065	AB-C5-M12MS-1,0PUR-M12FA	1	straight-angled	no	60	1
22260066	AB-C5-M12MS-2,0PUR-M12FA	2	straight-angled	no	60	1
22260067	AB-C5-M12MS-0,3PUR-M12FA-3L	0.3	straight-angled	3 LEDs	24	1
22260068	AB-C5-M12MS-0,6PUR-M12FA-3L	0.6	straight-angled	3 LEDs	24	1
22260069	AB-C5-M12MS-1,0PUR-M12FA-3L	1	straight-angled	3 LEDs	24	1

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

UNITRONIC® SENSOR M12-M12

Article number	Article designation	Length (m)	Design	LED	Rated voltage (V)	PU
22260070	AB-C5-M12MS-2,0PUR-M12FA-3L	2	straight-angled	3 LEDs	24	1
8-pin						
22260097	AB-C8-M12MS-0,3PUR-M12FS	0.3	straight-straight	no	30	1
22260098	AB-C8-M12MS- 0,6PUR-M12FS	0.6	straight-straight	no	30	1
22260099	AB-C8-M12MS-1,0PUR-M12FS	1	straight-straight	no	30	1
22260042	AB-C8-M12MS- 2,0PUR-M12FS	2	straight-straight	no	30	1
22260137	AB-C8-M12MS-0,3PUR-M12FA	0.3	straight-angled	no	30	1
22260138	AB-C8-M12MS-0,6PUR-M12FA	0.6	straight-angled	no	30	1
22260139	AB-C8-M12MS1,0PUR-M12FA	1	straight-angled	no	30	1
22260140	AB-C8-M12MS-2,0PUR-M12FA	2	straight-angled	no	30	1

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16