

UNITRONIC® SENSOR M12

M12 plug/socket on free conductor end

Sensor/Actuator-cable, connecting cable 3-pole, M12 connector/M12 socket on free conductor end, A-codiert, PUR LSZH, IP65/IP67/IP68, suitable for drag chains

Info

Other types are available at
www.lappgroup.com/assemblyfinder
 or on request



Supplementary automation components from Lapp



Mechanical and plant engineering



Space requirement



Power chain



Waterproof

Benefits

Cost-saving due to quick and easy installation
 Space-saving due to compact dimensions.
 Fast and easy error tracking
 Integrated vibration protection (mechanical lock-in)
 Gold-plated contacts for low transfer resistance

Application range

For increased mechanical stress and harsh operating conditions

Last Update (07.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12

Product features

UV-resistant
Good resistance to oils and chemicals
PWIS and PVC free
Suitable for drag chains
Including tag carrier

Norm references / Approvals

Halogenfree according to DIN VDE 0472
UL File Number: E249137
Flame-retardant according to UL 1581 FT-2

Product Make-up

wire cross-section: 0,34 mm²
(8-pin: 0,25 mm²)
Colour-code:
3-pin: bn (1), bu (3), bk (4)
4-pin: bn (1), wh (2), bu (3), bk (4)
5-pin: bn (1), wh (2), bu (3), bk (4), gn/ye (5)
8-pin: wh (1), bn (2), gn (3), ye (4), gy (5), pk (6), bu (7), rd (8)
Outer sheath: PUR, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001855 ETIM 5.0 Class-Description: Sensor-actuator patch cord
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001855 ETIM 6.0 Class-Description: Sensor-actuator patch cord
Material:	Contact: CuSn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: TPU, flame-retardant, self-extinguishing
Minimum bending radius:	Fixed installation: 5 x outer diameter Flexing: 10 x outer diameter
Protection rating:	IP65/IP67
Ambient temperature (operation):	Plug/socket -25 °C to +90 °C Fixed installation -40 °C to +80 °C Flexing -25 °C to +80 °C
Coding:	A-standard
Rated current (A):	4 A 2 A (8-pin)

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: inclusive of copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UL certifications can be found in the data sheet.

UNITRONIC® SENSOR M12

Article number	Article designation	Number of pins	Length (m)	Design	LED	Rated voltage (V)	PU
22260221	AB-C3-M12MS-2,0PUR	3	2	straight	no	250	1
22260222	AB-C3-M12MS-5,0PUR	3	5	straight	no	250	1
22260249	AB-C3-M12MS-10,0PUR	3	10	straight	no	250	1
22260223	AB-C3-M12MA-2,0PUR	3	2	angled	no	250	1
22260224	AB-C3-M12MA-5,0PUR	3	5	angled	no	250	1
22260256	AB-C3-M12MA-10,0PUR	3	10	angled	no	250	1
Socket							
22260257	AB-C3-2,0PUR-M12FS	3	2	straight	no	250	1
22260250	AB-C3-5,0PUR-M12FS	3	5	straight	no	250	1
22260251	AB-C3-10,0PUR-M12FS	3	10	straight	no	250	1
22260252	AB-C3-2,0PUR-M12FS-2L	3	2	straight	2 LEDs	24	1
22260265	AB-C3-5,0PUR-M12FS-2L	3	5	straight	2 LEDs	24	1
22260266	AB-C3-10,0PUR-M12FS-2L	3	10	straight	2 LEDs	24	1
22260258	AB-C3-2,0PUR-M12FA	3	2	angled	no	250	1
22260259	AB-C3-5,0PUR-M12FA	3	5	angled	no	250	1
22260260	AB-C3-10,0PUR-M12FA	3	10	angled	no	250	1
22260253	AB-C3-2,0PUR-M12FA-2L	3	2	angled	2 LEDs	24	1
22260254	AB-C3-5,0PUR-M12FA-2L	3	5	angled	2 LEDs	24	1
22260255	AB-C3-10,0PUR-M12FA-2L	3	10	angled	2 LEDs	24	1
22260320	AB-C4-M12MS-	4	2	straight	no	250	1

Last Update (07.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

UNITRONIC® SENSOR M12

Article number	Article designation	Number of pins	Length (m)	Design	LED	Rated voltage (V)	PU
	2,0PUR						
22260321	AB-C4-M12MS-5,0PUR	4	5	straight	no	250	1
22260342	AB-C4-M12MS-10,0PUR	4	10	straight	no	250	1
22260301	AB-C4-M12MA-2,0PUR	4	2	angled	no	250	1
22260302	AB-C4-M12MA-5,0PUR	4	5	angled	no	250	1
22260303	AB-C4-M12MA-10,0PUR	4	10	angled	no	250	1
Socket							
22260322	AB-C4- 2,0PUR-M12FS	4	2	straight	no	250	1
22260323	AB-C4- 5,0PUR-M12FS	4	5	straight	no	250	1
22260343	AB-C4-10,0PUR-M12FS	4	10	straight	no	250	1
22260344	AB-C4- 2,0PUR-M12FS-2L	4	2	straight	2 LEDs	24	1
22260345	AB-C4- 5,0PUR-M12FS-2L	4	5	straight	2 LEDs	24	1
22260346	AB-C4-10,0PUR-M12FS-2L	4	10	straight	2 LEDs	24	1
22260324	AB-C4- 2,0PUR-M12FA	4	2	angled	no	250	1
22260325	AB-C4- 5,0PUR-M12FA	4	5	angled	no	250	1
22260341	AB-C4-10,0PUR-M12FA	4	10	angled	no	250	1
22260326	AB-C4- 2,0PUR-M12FA-3L	4	2	angled	3 LEDs	24	1
22260327	AB-C4- 5,0PUR-M12FA-3L	4	5	angled	3 LEDs	24	1
22260340	AB-C4-10,0PUR-M12FA-3L	4	10	angled	3 LEDs	24	1
22260400	AB-C5-M12MS-2,0PUR	5	2	straight	no	60	1
22260401	AB-C5-M12MS-5,0PUR	5	5	straight	no	60	1

Last Update (07.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

UNITRONIC® SENSOR M12

Article number	Article designation	Number of pins	Length (m)	Design	LED	Rated voltage (V)	PU
22260414	AB-C5-M12MS-10,0PUR	5	10	straight	no	60	1
22260402	AB-C5-M12MA-2,0PUR	5	2	angled	no	60	1
22260403	AB-C5-M12MA-5,0PUR	5	5	angled	no	60	1
22260417	AB-C5-M12MA-10,0PUR	5	10	angled	no	60	1
Socket							
22260404	AB-C5- 2,0PUR-M12FS	5	2	straight	no	60	1
22260405	AB-C5- 5,0PUR-M12FS	5	5	straight	no	60	1
22260415	AB-C5-10,0PUR-M12FS	5	10	straight	no	60	1
22260406	AB-C5- 2,0PUR-M12FA	5	2	angled	no	60	1
22260407	AB-C5- 5,0PUR-M12FA	5	5	angled	no	60	1
22260418	AB-C5-10,0PUR-M12FA	5	10	angled	no	60	1
22260408	AB-C5- 2,0PUR-M12FA-3L	5	2	angled	3 LEDs	24	1
22260409	AB-C5- 5,0PUR-M12FA-3L	5	5	angled	3 LEDs	24	1
22260416	AB-C5-10,0PUR-M12FA-3L	5	10	angled	3 LEDs	24	1
22260091	AB-C8-M12MS-2,0PUR	8	2	straight	no	30	1
22260092	AB-C8-M12MS-5,0PUR	8	5	straight	no	30	1
22260093	AB-C8-M12MS-10,0PUR	8	10	straight	no	30	1
22260094	AB-C8-M12MA-2,0PUR	8	2	angled	no	30	1
22260095	AB-C8-M12MA-5,0PUR	8	5	angled	no	30	1
22260096	AB-C8-M12MA-10,0PUR	8	10	angled	no	30	1

Last Update (07.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

UNITRONIC® SENSOR M12

Article number	Article designation	Number of pins	Length (m)	Design	LED	Rated voltage (V)	PU
Socket							
22260726	AB-C8-2,0PUR-M12FS	8	2	straight	no	30	1
22260728	AB-C8-5,0PUR-M12FS	8	5	straight	no	30	1
22260729	AB-C8-10,0PUR-M12FS	8	10	straight	no	30	1
22260141	AB-C8-2,0PUR-M12FA	8	2	angled	no	30	1
22260615	AB-C8-5,0PUR-M12FA	8	5	angled	no	30	1
22260616	AB-C8-10,0PUR-M12FA	8	10	angled	no	30	1

Last Update (07.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

UNITRONIC® SENSOR M12

