

EPIC® SENSOR CCR

Cable coupler round, shielded for e.g. sensor-actuator / PROFIBUS / CAN cables

Field mountable round cable coupler, IP67, IDC, for CAN / Profibus / sensor-actuator applications, 360° shielding



Devicesafe CANopen



Waterproof



Interference signals



Mechanical and plant engineering



Kompletterande automationskomponenter från Lapp

Benefits

Optimum EMC protection with 360 ° shielding
Time-saving assembly with IDC connection technology

Application range

To extend existing cable systems
Repairkit for damaged cables

Product features

5-pin cable coupler round
Screened version

Technical Data

Material:

Contact: CuZn
Contact surface: Ni/Au
Knurl: Zinc die-cast, nickel-plated
Gripping body: Zinc die-cast, nickel-plated

Protection rating:

IP65/IP67

Last Update (07.01.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SENSOR CCR

Ambient temperature (operation):	-40°C to +85°C
Rated current (A):	4 A

Note

DeviceNet is a registered trademark of ODVA

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SENSOR CCR

Article number	Article designation	Number of pins	Cross-section in mm ²	Cable diameter in mm	Rated voltage (V)
Cable coupler round					
21700641	AB-C5-CCR-SH	5	18.0 - 26.0	5.0 - 9.7	60

Last Update (07.01.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16