

EPIC® POWER LS1.5 Contacts female

Contacts, tools, accessories for circular connectors

EPIC® POWER LS1.5 Contacts female for size 1.5 circular connector series

Info

All contacts are high quality gold plated

Slotted contacts with external pressure spring

Made in Germany



Good chemical resistance



Corrosion-resistant



Mechanical resistance



Optimum strain relief



Robust



Reliability

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (24.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWER LS1.5 Contacts female

Article number	Article designation	Version	For design	Pieces / PU
3.6 mm female contacts				
44429318	LS1.5 D BCEM 3,6MM AU 1,0-2,5	3.6 mm female 1.0 - 2.5 mm ²	for type D6, A6	10
44429319	LS1.5 D BCEM 3,6MM AU 2,5-4,0	3.6 mm female 2.5 - 4.0 mm ²	for type D6, A6	10
44429320	LS1.5 D BCEM 3,6MM AU 4,0-6,0	3.6 mm female 4.0 - 6.0 mm ²	for type D6, A6	10
44429321	LS1.5 D BCEM 3,6MM AU 6,0-10,0	3.6 mm female 6.0 - 10.0 mm ²	for type D6, A6	10
2 mm female contacts				
44429322	LS1.5 D BCEM 2MM AU 0,25-1,0	2 mm female 0.25 - 1.0 mm ²	for type D6, A6	10
44429323	LS1.5 D BCEM 2MM AU 0,75-1,5	2 mm female 0.75 - 1.5 mm ²	for type D6, A6	10
44429324	LS1.5 D BCEM 2MM AU 1,0-2,5	2 mm female 1.0 - 2.5 mm ²	for type D6, A6	10
44429325	LS1.5 D BCEM 2MM AU 4,0	2 mm female 4.0 mm ²	for type D6, A6	10

Last Update (24.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16