

EPIC® POWERLOCK A6 C

Single-pin circular connector for mobile power distribution, electro motors and generators

EPIC®POWERLOCK Panel base source 660A for crimp connection up to 240mm²

Info

Connector for unscreened single-core power cables



Waterproof



Reliability



Robust



Optimum strain relief



Wide clamping range

Benefits

Resistant to mechanical influences in harsh environmental conditions

Connectors in harmonised colours according to European standards

Every colour has a different coding to prevent incorrect plugging

Application range

For renewable energy plants e.g. wind power

For mobile and stationary power distribution

For the connection of motors, transformers and generators

Light & sound technology

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWERLOCK A6 C

Product features

Panel-mount base, straight entry, flat gasket included
Contact fixing by contact retention pin, each pin can only be used once
Housing without contact, order contact separately

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Rated voltage (V):	1000 V
Rated impulse voltage:	8 kV
Rated current (A):	Max. crimp 660 A
Pollution degree:	3
Contacts:	Crimp termination: copper, silver-plated
Number of contacts:	1
Termination methods:	Crimp termination: 35 - 240 mm ²
Material:	Housing: PBT Contact retention pin: PA
Protection rating:	IP 67 (maximum, dependant on cable gland used) IP 20 (unmated)
Cycle of mechanical operation:	500
VDE-tested:	VDE Reg. No. D42
Temperature range:	-25°C up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® POWERLOCK A6 C

Article number	Article description	Fastening type	Pin configuration
44420226	POWERLOCK A6 PE/GN	Ø 5.5 mm (4x)	PE, Green
44420227	POWERLOCK A6 N/BL	Ø 5.5 mm (4x)	N, Blue
44420228	POWERLOCK A6 L1/BN	Ø 5.5 mm (4x)	L1, Brown
44420229	POWERLOCK A6 L2/BK	Ø 5.5 mm (4x)	L2, Black
44420230	POWERLOCK A6 L3/GY	Ø 5.5 mm (4x)	L3, Grey
For direct current applications in conjunction with L2/black			
44420317	POWERLOCK A6 L1/RD	Ø 5.5 mm (4x)	L1, Red

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWERLOCK A6 C

