

EPIC® SIGNAL M23 Contacts female

Contacts, tools, accessories for circular connectors M23


EPIC® SIGNAL M23 Contacts female for M23 circular connector series

Info

All contacts are high quality gold plated

Contacts are designed for wide crimping range, therefore low number of variants

Made in Germany



Good chemical resistance



Corrosion-resistant



Mechanical resistance



Oil-resistant



Optimum strain relief



Robust



Reliability

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SIGNAL M23 Contacts female

Article number	Article designation	Version	For design	Pieces / PU
1mm contacts, female				
74020601	-	1 mm female slot 0.14 - 1.0 mm ²	per inserts M23 (not D-Sub), LS1 D6, LS1 A6	10
74200600	-	1 mm female slot 0.14 - 1.0 mm ²	per inserts M23 (not D-Sub), LS1 D6, LS1 A6	100
72402601	-	1 mm female slot solder	M23 inserts (not D-Sub)	10
72402600	-	1 mm female slot solder	M23 inserts (not D-Sub)	100
74034500	-	1 mm female hyperboloid 0.14 - 1.0 mm ²	per inserts M23 (not D-Sub), LS1 D6, LS1 A6	100
74034501	-	1 mm female hyperboloid 0.14 - 1.0 mm ²	per inserts M23 (not D-Sub), LS1 D6, LS1 A6	10
2mm contacts, female				
72401601	-	2 mm female 1.0 - 2.5 mm ²	M23 inserts (not D-Sub)	10
72401600	-	2 mm female 1.0 - 2.5 mm ²	M23 inserts (not D-Sub)	100
72404100	-	2 mm female solder	M23 inserts (not D-Sub)	10
72404000	-	2 mm female solder	M23 inserts (not D-Sub)	100

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SIGNAL M23 Contacts female

