

EPIC® H-A 16 TGH

These connectors are attractive because of their compact housing.


Small and compact high metal housing has pivots for a single lever and a direct cable entry and can be used, for example, in control systems.

Info

Non-slip ridges for comfortable disconnecting

More interior space for wiring

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Small and compact, for applications with high number of contacts

Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

Product features

Hood, high version

Bolts for single lever

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 16 TGH

Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® H-A 16 TGH

Article number	Article description	M	PG	Neck	Pieces / PU
H-A housing: hood (straight cable entry, bolts for single lever, high version)					
70490200	H-A 16 TGH 16	-	16	yes	5
70490400	H-A 16 TGH 21	-	21	yes	5
79490200	H-A 16 TGH M20	20	-	-	5
79490400	H-A 16 TGH M25	25	-	-	5