

EPIC® MC 2.5 stamped contacts-on-reel

For inserts and modules of the EPIC® rectangular connectors

The stamped contacts are coiled up in reels of 100 or 200 pieces for use with conductor cross-sections from 0.5 to 1.5 mm² and 1.5 to 2.5 mm².

Info

silver plated and passivated contacts
for very fast crimping with Hand crimping tool for contacts on reel
Two crimp areas with wire and insulation crimp



Product features

Stamped crimping contact silver plated on small reel
use Hand crimping tool 11147005 for cross section from 0.5 to 1.5mm²
use Hand crimping tool 11147006 for cross section from 1.5 to 2.5mm²

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC 2.5 stamped contacts-on-reel

Article number	Article description	Contact type	Conductor cross-section (mm ²)	Surface	Stripping length (mm)	Note	Pieces / PU
Contacts							
11208000	EPIC® MC SCBG AG 0.5-1.5 200 LI	male	0.5 - 1.5	Ag	3.5 + 0.5	1 reel (PU) = 200 contacts	1
11209000	EPIC® MC BCBG AG 0.5-1.5 200 LI	female	0.5 - 1.5	Ag	3.5 + 0.5	1 reel (PU) = 200 contacts	1
11208500	EPIC® MC SCBG AG 1.5-2.5 100 LI	male	1.5 - 2.5	Ag	3.5 + 0.5	1 reel (PU) = 100 contacts	1
11209500	EPIC® MC BCBG AG 1.5-2.5 100 LI	female	1.5 - 2.5	Ag	3.5 + 0.5	1 reel (PU) = 100 contacts	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16