

## EPIC® H-B 10 TBFH

Housing design H-B. The industry standard.

The robust high metal housing consists of 2 double levers and a direct cable entry and is suitable for use in the plastics industry.

### Info

More interior space for wiring

Double lever version with 2 levers for increased safety



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

The smallest housing with single and double lever. The right housing is available for every application

### Application range

Plant engineering

Light & sound technology

Plastics industry

### Product features

Cable coupler hood, high version

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-B 10 TBFH

Dual levers  
Straight cable entry  
Versions with / without neck

### Technical Data

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437<br>ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437<br>ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material:              | Housing: powder-coated aluminium alloy, grey<br>Lever: zinc-plated steel<br>Sealing: NBR     |
| Protection rating:     | IP 65 (latched)<br>NEMA 250, UL50E: 12, 4 (latched)  |
| VDE-tested:            | Certified production control: VDE-REG. no.: B437<br>UL-tested:<br>UL File Number: E75770     |
| Temperature range:     | -40 °C to +100 °C, short-term up to +125 °C  |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-B 10 TBFH**

| Article number   | Article description | M  | PG | Neck | Pieces / PU |
|--|---------------------|----|----|------|-------------|
| H-B housing: cable coupler hood (straight cable entry, double lever, high version) |                     |    |    |      |             |
| 70040400   | H-B 10 TBFH 21      | -  | 21 | yes  | 10          |
| 70040600   | H-B 10 TBFH 29      | -  | 29 | yes  | 10          |
| 79040400   | H-B 10 TBFH M25     | 25 | -  | -    | 10          |
| 79040600   | H-B 10 TBFH M32     | 32 | -  | -    | 10          |