

## EPIC® H-A 3 MAGD


Innovative metal and plastic housing design

The compact metal housing for rectangular connectors is supplied with a seal and it is suitable for control systems.

### Info

Metal lid with sturdy hinge

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

Housing in plastic or metal version for safe connections in the smallest possible space

### Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

### Product features

H-A case: Wall base

1 lever

Metal cover

Included: flat gasket

Last Update (10.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-A 3 MAGD

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated zinc die-casting, grey Lever: zinc-plated steel Sealing: NBR Metal cover
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## EPIC® H-A 3 MAGD

Article number	Article description	M	Material	Colour	Pieces / PU
H-A housing: panel-mount base with cover (with sealing, for female inserts)					
44429015	EPIC® H-A 3 MAGD	AG	Aluminium die-casting	grey	10