

## EPIC® H-A 3 MTGVB

Innovative metal and plastic housing design

The metal housing for placement in rectangular connectors can be selected with or without a cable outlet.

### Info

Small, rugged metal housing

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

The EPIC® H-A 3 series comprises the smallest housings in the heavy-duty industrial connector range and ensures secure connections in the smallest of spaces.

The coupling housing is mateable with many commercially available hood housings.

The integrated SKINTOP® cable gland made of brass is used for sealing and strain-relieving cable entry. Compared to enclosures where the cable gland is added separately, the overall size of the enclosure is more space-saving.

The locking is done single lever.

The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.

### Application range

To protect the connector insert from environmental influences.

For use with many EPIC® rectangular connector inserts.

For power supply connection of devices and machines in various applications.

Last Update (08.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-A 3 MTGVB

Withstands high environmental and mechanical stresses.

### Product features

Cable coupler hood  
1 lever  
Straight cable entry  
Versions with / without cable gland

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated zinc die-casting, grey Lever: zinc-plated steel
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-A 3 MTGVB**

Article number	Article description	M	PG	Material	Colour	Cable gland	Cable clamping range	Pieces / PU
H-A housing: cable coupler hood (straight cable entry)								
10512900	H-A 3 MTgvb	-	11	Zinc die-casting	grey	-	-	10
10429500	H-A 3 MTgvb	-	11	Zinc die-casting	grey	yes	6.5 - 12	10
19512900	EPIC® H-A 3 MTgvb M20	20	-	Zinc die-casting	grey	-	-	10
19429500	EPIC® H-A 3 MTgvb M20	20	-	Zinc die-casting	grey	yes	3.0 - 13.5	10

Last Update (08.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16

**EPIC® H-A 3 MTGVB**

