
EPIC® H-A 32 TBF

Rugged housings for 2 inserts

Control systems and machine and device manufacturing are two areas for which the metal housing with 2 narrow inserts for rectangular connectors is ideally suited.

Info
Compact, robust metal housings for double size H-A 32



- Mechanical and plant engineering
- Mechanical resistance
- Robust
- Waterproof

Benefits
For two inserts of the small H-A, H-D and STA series. Space-saving

Application range
Machine and equipment manufacturing
Control engineering

Product features
Cable coupler hood
Dual levers
Straight cable entry
Versions with / without neck

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-A 32 TBF

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

LAPP

EPIC® H-A 32 TBF

PRODUCT INFORMATION

Article number	Article description	M	PG	Neck	Pieces / PU
H-A housing: cable coupler hood (straight cable entry, double lever)					
10588000	H-A 32 TBF 21	-	21	yes	5
10588500	H-A 32 TBF 29	-	29	yes	5
19588000	H-A 32 TBF M25	25	-	-	5
19588500	H-A 32 TBF M32	32	-	-	5

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16