

## EPIC® H-B 6 TG

Housing design H-B. The industry standard.

The universal metal housing is the smallest body in the H-B series and is suitable for inserts with outstanding electrical properties.

### Info

Non-slip ridges for comfortable disconnecting  
 High version: More interior space for wiring  
 Protection rating UL50E tested



Waterproof



Robust



Mechanical resistance



Mechanical and plant engineering



Supplementary automation components from Lapp

### Benefits

The smallest housing out of the H-B series. For inserts with high electrical properties

### Application range

Plant engineering  
 Control engineering  
 Plastics industry

## EPIC® H-B 6 TG

### Product features

Hood, low version  
Bolts for single lever  
Straight cable entry  
Versions with / without neck

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Bolts: steel, coated
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-B 6 TG**

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (straight cable entry, bolts for single lever)					
10011000	H-B 6 TG 13,5	-	13.5	yes	10
10021000	H-B 6 TG 16	-	16	yes	10
19011000	H-B 6 TG M20	20	-	-	10
19021000	H-B 6 TG M25	25	-	-	10

Last Update (01.08.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16