

EPIC® H-B 6 TSH

Housing design H-B. The industry standard.

The robust metal housing with pivots for a single lever and a side cable entry is suitable for use in the plastics industry and investment construction.

Info

- Non-slip ridges for comfortable disconnecting
- More interior space for wiring
- Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The smallest housing out of the H-B series. For inserts with high electrical properties

Application range

- Plant engineering
- Control engineering
- Plastics industry

Product features

Last Update (19.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 6 TSH

Hood, high version
Bolts for single lever
Side cable entry
Versions with / without neck

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | Housing: powder-coated aluminium alloy, grey Bolts: steel, coated |
| Protection rating: | IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770 |
| Temperature range: | -40°C to +100°C, short-term up to +125°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® H-B 6 TSH

| Article number | Article description | M | PG | Neck | Packaging unit |
|--|---------------------|----|----|------|----------------|
| H-B housing: hood (side cable entry, bolts for single lever, high version) | | | | | |
| 70022200 | H-B 6 TSH 21 | - | 21 | yes | 10 |
| 70022400 | H-B 6 TSH 29 | - | 29 | yes | 10 |
| 79022200 | H-B 6 TSH M25 | 25 | - | - | 10 |
| 79022400 | H-B 6 TSH M32 | 32 | - | - | 10 |

Last Update (19.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16