

EPIC® H-B 16 TBF

Housing design H-B. The industry standard.

The robust metal housing for use in investment construction consists of a direct cable entry and 2 double levers.

Info

Double lever version with 2 levers for increased safety

Protection rating UL50E tested



Waterproof



Robust



Mechanical resistance



Mechanical and plant engineering



Supplementary automation components from Lapp

Benefits

The housing standard. Wide choice for all applications

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

Cable coupler hood, low version

Last Update (07.08.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 16 TBF

Dual levers
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 16 TBF

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: cable coupler hood (straight cable entry, double lever)					
10086000	H-B 16 TBF 21	-	21	yes	5
19086000	H-B 16 TBF M25	25	-	-	5

Last Update (07.08.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16