

## EPIC® H-Q 5

Product discontinued, replacement product available

The compact and powerful standard insert is a favourite thanks to its cost-saving crimping contact.


### Info

Compact, powerful standard insert  
Space saving, crimping contact  
Made in Europe



M

F



Supplementary automation components from Lapp



Mechanical and plant engineering

### Benefits

Mateable with market standard connectors.  
High performance crimping contacts  
PE contact with screw connection

### Application range

Machine and equipment manufacturing  
Control engineering

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000438

ETIM 5.0 Class-Description: Contact insert for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000438

ETIM 6.0 Class-Description: Contact insert for industrial connectors

Rated voltage (V):

IEC: 230 V / 400 V

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**EPIC® H-Q 5**

	UL: 600 V CSA: 600 V
Rated impulse voltage:	4 kV
Rated current (A):	IEC: 16 A UL: 16 A CSA: 16 A
Pollution degree:	3
Flammability:	UL94 V-0
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver/gold-plated
Number of contacts:	5 + PE
Termination methods:	Crimp termination: 0.5 - 2.5 mm <sup>2</sup>
Material:	PBT Polyester
Cycle of mechanical operation:	100
Temperature range:	-40°C to +100°C, short-term up to +125°C

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-Q 5**

Article number	Article description	Contact type	Number of operating contacts	Pieces / PU
10432500	H-Q 5 BC	female	1 - 5	10

## EPIC® H-Q 5

